



### FEATURES:

- Adapter converts Double Banana Jack Test Instruments to BNC Coaxial configuration for added shielding protection.
- For test versatility, banana plugs can be vertically and horizontally stacked to the adapter.
- Banana Plug springs feature Nickel Plated, Beryllium Copper for tarnish resistance & long insertion life.
- The BNC center contact is Gold Plated, Brass for low contact resistance
- The BNC shell is plated for tarnish resistance.

### MATERIALS:

BNC (Male): Body: Brass, Nickel Plated  
Center Contact: Brass, Gold Plated  
Impedance: 50 Ohms

Banana Plug: Body: Brass, Nickel Plated  
Spring: Beryllium Copper, Nickel Plated

Insulation: ABS Molded to BNC (Male) and Banana Plug Bodies, Color: Black  
Marking: "1270 POMONA"

### RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 500 VRMS Max.

Operating Temperature: +50°C (+122°F) Max.

### ORDERING INFORMATION: Model 1270

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90498 (800) 444-6785 or (424) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)