



MATERIALS:

Body and Fittings - Brass
Center Contact – Gold Plated Brass
Connector meets the interface requirements of MIL-STD-348.
Gasket: Silicone rubber

Finish:

Body and Fittings – White Bronze Plating
Center Contact – Gold Plated Brass

RATINGS:

Operating Voltage: 1000 VRMS
Nominal Impedance: 50 Ohms
Dielectric – PTFE

ORDERING INFORMATION: Model 3842

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA