



FEATURES:

- To ensure accurate low voltage or high resistance precision measurements, Pomona's durable Model 2305 features heavy duty construction with a gold plated tellurium copper base.
- The tellurium copper/gold material combination offers superior conductivity and low oxide build-up and minimizes the thermoelectric effect, thus ensuring accurate readings in the nano-volt or 10^9 ohmic range.
- The spade lug attaches to shunt terminals, standard binding posts or 1/4" screws. For meter attachment, the Model 2305 is designed with an insulated standard banana jack which will interface to Pomona's Low EMF Retractable Sheath Banana Plug Cord Model 5291.

MATERIALS:

Spade Lug Body – Tellurium Copper, Alloy 145, Gold Plated per MIL-G-45204

Banana Jack – Tellurium Copper, Alloy 145, Gold Plated per MIL-G-45204

Insulation – ABS Molded to Banana Jack and Spade Lug Body

Colors: Black and Red,

Marking: "Pomona Electronics, Calif."

RATINGS:

Operating Temperature: +50°C (+122°F)

Operating Voltage – 5000 VDC

Current: 15 Amperes

ORDERING INFORMATION: Model 2305

Package includes one black, one red spade lug

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA