



FEATURES:

- Adapts banana jack test instruments for BNC Cable Assemblies.
- Banana plug spring is nickel-plated Beryllium Copper and BNC spring is gold plated Beryllium Copper for low contact resistance and long insertion life.
- Schematic: BNC center contact to Banana Plug, BNC shell is a no connect.

MATERIALS:

BNC Female: Body – Brass, Nickel Plated, Female Spring – Beryllium Copper, Gold Plated.

Insulation: ABS, Color – Black, Marking: “1894 Pomona Electronics, Calif.”

Banana Plug: Body – Brass, Nickel Plated, Spring – Beryllium Copper, Nickel Plated

RATING:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 500 VRMS Max.

Operating Temperature: +50°C (+122°F)

ORDERING INFORMATION: Model 1894

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA