



### FEATURES:

- Fits standard banana plug.
- 1/4 - 32 Thread

### MATERIAL:

Banana Jack Body – Nickel Plated Brass

Solder Lug – Copper, finish – Hot tin dip

Hex Nut – Brass - 6.35 (.250) –23 Double Chamfered, Nickel Plated

### RATING:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 2500 WVDC Max.

Current: 15 Amperes Cont.

### ORDERING INFORMATION: Model 3267

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm$ .02" (.51 mm), .xxx =  $\pm$ .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA