



### FEATURES:

- ✓ Ideal test adapters for rapid testing of the hard-to-get to pins of multi-pin connectors.
- ✓ Flexible tip allows testing of adjacent contacts.
- ✓ Full insulation protects against shorting or contact damage.
- ✓ Model 4690 will also slip over 0.025" (0.63mm) square pins.

### MATERIALS:

Insulation: Polyvinyl chloride (PVC)  
Banana Jack Body (upper connector)

*Material:* Brass.

*Finish:* Bright Tin plated

Socket (lower connector):

*Material:* Copper Alloy

*Finish:* Gold over copper plate

Model	Contact Size	Type	Current
4690	22 AWG .030" (.76mm)	Socket	5 Amps
3560	20 AWG .040" (1.02mm)	Socket	7.5 Amps
3562	16 AWG .063" (1.60mm)	Socket	13 Amps
3564	12 AWG .093" (2.36mm)	Socket	24 Amps

### Ratings:

Hands free testing in controlled voltage environments:  
2500 Vrms Max. *For CE compliance:* not intended for  
hand-held use at voltages above 33 Vrms/70 Vdc.  
Operating Temperature: +131F (+55C) Max.

### ORDERING INFORMATION: Model: 3560-\*, 3562-\*, 3564-\*, 4690-\*

\*=Color, -0 Black, -2 Red    Ordering Example: 3560-2 (red adapter)

*Test Kit 6481:* contains 18 pieces, one red and one black adapter of each adapter; 3560, 3561, 3562, 3563, 3564, 3565, 4690, 4691 and one set of model 6358 test leads.

*For banana jack to test pins, see models: 3561, 3562, 3565, 4691*

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)

For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)