



MATERIALS:

Upper Conn.: Banana Jack

Brass per QQ-B-626, Alloy 360, 1/2 Hard.

Finish: Nickel plated per Q-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene (fire retardant) molded to Banana Jack Body. Color : See Tab Block.

Marking: "POMONA"

Lower Conn.: Spade Lug

Material: Copper.

Finish: Electro-tin plated.

RATINGS:

Operating Temperature: +50° C (+122° F) Max.

Operating Voltage 5000 VDC

Current 15 Amperes

ORDERING INFORMATION: See table above

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA