



MATERIALS:

Body – Gold Plated Beryllium Copper, Male Contact – Gold Plated Brass, Female Contact – Gold Plated Beryllium Copper

Dielectric: Teflon per L-P-403

Finish: Body and Contacts – Gold Plated per MIL-G-45204, Type II, Class 2

Marking: “Pomona 4290”

RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Contuictor/Shield: 335VRMS Max.

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

Nominal Impedance: 50 Ohms

Frequency Range: 0-12.4 GHz.

ORDERING INFORMATION: Model 4290

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90247 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com