
# Pomona®

## Model 5058 SMA Male To Type "N" Male 50 Ohm Cable Assembly



#### **FEATURES:**

- Provides a simple means of connection between equipment with both SMA and Type N jacks.
- SMA and N connectors feature PTFE dielectric and tarnish resistant shells for superb electrical performance.
- Gold center contacts assure noise free connections.

#### **MATERIALS:**

Type N Male: Body and Fittings – Brass, Tarnish Resistant

Center Contact – Brass, Gold Plated

Dielectric - PTFE

Coaxial Cable: RG142B/U, Double Shielded, O.D. .195" (4,95mm) SMA Male: Body and Fitting – Steel, Finish – Passivated Steel

Center Contact – Brass, Gold Plated

Dielectric – PTFE

### **RATINGS:**

Operating Temperature: +200°C (+329°F) Max.

Operating Voltage: 335 VRMS Max. Connector/Cable Impedance: 50 Ohms

#### **ORDERING INFORMATION:** Model 5058-X-xx

xx = Cable Length in Inches, Standard Lengths: 12" (30.48cm), 24" (61cm), 36" (91,44cm), 48" (122cm), 60" (152,4cm)

Additional lengths can be quoted upon request.

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA