



MATERIALS:

BNC Male

Body and Fittings – Brass per QQ-B-626, Alloy 360, ½ Hard.

Center Contact – Brass per QQ-B-626, Alloy 360, ½ Hard.

Dielectric – Teflon per ASTM D1457.

Vee Gasket – Silicone rubber per QQ-R-765, Class 11A, Grade 50.

Clamp Nut – Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish:

Body and Fittings – Tarnish resistant

Center Contact – Gold plated per requirements of MIL-C-39012

Clamp Nut – Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Stress Relief Boot

Boot – PVC. Marking: “POMONA ELECTRONICS”

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 500 VRMS

ORDERING INFORMATION: Model 5068-*

*= Color, Standard Colors: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA