



FEATURES:

- Fits Fluke, HP, Tektronix and Wavetek meters configured with non-sheathed standard and 4 mm banana jacks.
- Test probe body & banana plug body are molded directly to 48" (122 cm) high strand count/high temperature silicone leads for added pull strength and flexibility.
- Medium alligators are insulated for added safety and can quickly attach to the .080" (2.03 mm) O.D. probe tip.
- Medium alligators have an overall length of 2.25" (5.7 cm) and grip up to 0.30" (7.62 mm) O.D. terminals.
- Slide-on extended tips have an overall length of 4" (10.16 cm) & attaches to the probe tip to allow access to hard to reach test points.
- Slide-on Extended Tip is insulated to the point to prevent accidental shorting.

Kit Accessories: Model **6343**: Test Probes, set of one black and one red. Model **5682**: Slide-on Extended Tip, set of one black and one red (Replacement P/N: 5682-0/-2) Model **5916A**: Medium Alligators, set of one black and one red. (Replacement P/N: 5916A).

MATERIALS:

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Model: **6343**: Over molded Probe Test Lead w/ sheathed right Angle banana plugs:

Probe body and banana plug body: Polypropylene – Fire Retardant, Tip: Stainless Steel

Wire: 18 AWG, 65 x 36 Tinned Copper Strand, Silicone Insulation, O.D. 0.144" (3.7 mm). Length: 48" (122 cm)

Banana Plug: Insulation: Polypropylene – Fire Retardant, Plug Body: Brass Nickel Plated, Spring: Beryllium Copper, Nickel Plated, **RATINGS**: Operating Voltage: 1,000 VAC/DC, Current: 10 Amps

Model: **5682**: Probe Extended Tip Adapter:

Insulation – Polypropylene , Fire Retardant, Color: one black and one red

Probe Tip: Stainless Steel With Kynar Insulation Sleeve To Tip End, **RATINGS**: +80°C. (+176°F.) Max.

Model: **5916A**: Medium Alligator

Insulation: Polypropylene, fire retardant, UL94 V-2 Rated, Color: One Black, One Red

Body: Steel, Nickel Plated, Spring: Music Wire, **RATINGS**: 300 VRMS, Current: 5 Amperes

ORDERING INFORMATION: Model 5672A Kit shipped in a reusable plastic case.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA