



### FEATURES:

- Same high quality construction as 2249-C without molded strain relief.

### MATERIALS:

Conn: 1<sup>st</sup> End-BNC Male

Impedance: 50 Ohms

Material: Body and Center Contact – Brass

Finish: Body: Tarnish Resistance

Center Contact: Gold Plated

Cable: RG58C/U

Impedance: 50 Ohms

O.D.: (0.195)

Marking: "POMONA 5697"

Conn: 2<sup>nd</sup> End-Same as first end

### RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +80°C. (+176°F.) Max.

### ORDERING INFORMATION: Model 5697-XX

XX=Cable Length, Standard Length: 12" (305), 18" (457), 24" (610), 36" (914), 48" (1219), 60" (1524), 72" (1829), 96" (2438), 120" (3048), 144" (3658), 180" (4572), 240" (6096), 300" (7620), 360" (9144), 600" (15240)

Ordering Example: 5697-240 indicates 240" in length.