
# Pomona

# **Model 6387** Banana Jack, Panel Mount, 4mm For Sheathed Banana Plugs



Recommended Maximum Panel Thickness: .57" (15mm)

#### **FEATURES:**

- Banana Jack mates to all popular shrouded and unshrouded DMM plugs •
- Meets IEC 1010-2-031 CAT III 1000V

## **MATERIALS:**

Banana Jack: Brass, see ordering information for plating Insulation: Nylon, see ordering information for color Nut: Brass, Nickel Plated

## **RATINGS:**

Operating Voltage: 1000 VRMS Max. Current: 15 Amperes Max.

**ORDERING INFORMATION:** Model 6387-T-P-C. Sold in packs of ten.

T = Terminal Type = ST = (Solder Turret), BC = (Bifurcated Cup),TS8=(Threaded Stud #8-32) P = Plating Options = T = (Tin), G = (Gold), N = (Nickel)C = Color Options = See below.6387-BC-G and 6387-TS8-N available in 0-Black, 2-Red 6387-ST-T available in 0-Black, 2-Red, 5-Green, 6-Blue, 8-Gray, 9-White

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA