



### FEATURES:

- Extra large Alligator features a 0.8" (20mm) jaw opening
- Strain reliefs are on clip and plug ends for added pull strength
- Designed to comply with IEC 1010, which is an international safety standard

### MATERIALS:

Alligator: Jaw: Nickel steel

Insulation: Polyamide

Wire: 18 AWG, Silicone jacket

Plug: Body: Brass, nickel plated

Spring: Beryllium Copper

### RATINGS:

CAT III, 1000V, 20 Amperes

### ORDERING INFORMATION: Model 6570-XX-\*

XX = Wire Length, Standard Length: 36" (91cm), 60" (152cm)

\* = Standard Colors, -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA