



1300 Series Open Barrel Non-Insulated Terminal Crimper - 1306

Part number: 1306 Technical

Part numbers

Tool & Die: 1306

Die only: 2033

Description

Crimps 22-10 AWG (.34-2.5 mm²) open barrel, narrow, non-insulated terminals and lugs for standard commercial terminals.

Type

22-10 AWG (.34-2.5 mm²) stranded wire

Crimp size

22-18/16-14/12-10

Connector style

Open barrel, non-insulated terminals & lugs; F-Type or B-Type



PowerPlay®
PT-525



Ultimate
Technician
Tool Kit



RG6/RG6Q &
Cat5e, Cat6
CrimpAll
Crimper



Combo
UTP/Coax
SureStrip®
Cutter/Stripper



CoaxReady™
Compression
Tool Kit