



## 1600 Series Professional Wire Ferrule Crimper

Part number: 1647 Technical

### Part numbers

Tool & Die: 1647

Die only: 2681

### Description

Professional-quality crimping tool for insulated and non-insulated wire ferrules with a range of 20-10 AWG (0.5-6.0 mm<sup>2</sup>).

### Features

- Ferrules' crimp conforms to DIN 46228 Pt. 1 and 4
- Ferrule insertion from the side of the tool
- Single tool for entire wire range (no additional dies are required)
- Durable steel construction for long life
- Ergonomic handles for low-effort operation

### Type

20-10 AWG (.5-6 mm<sup>2</sup>) stranded wire

### Crimp size

20-10 Trapezoid

### Connector style

DIN or US type wire ferrules

### Connector type

Insulated & non-insulated wire ferrules

### We also suggest



SealTite® Pro for the Smart Home A/V Kit



CST Pro Coax Stripper 3-Level (Green Cassette: .279/.201)



SealTite® ProM Coax Crimper



LAN & A/V Cable-Check™



PowerPlay® PT-540