



Die for CrimpALL/8000 & 1300 Series Non-Insulated Terminal & Lug - 2096

Part number: 2096

Description

Crimps 22-14 AWG (.34-2.5 mm² wide, open barrel, non-insulated terminals & lugs for standard commercial terminals.

Type

22-14 AWG (.34-2.5 mm²) stranded wire

Crimp size

16-14/22-18

Connector style

Open barrel, non-insulated terminals & lugs; F-Type or B-Type



SealTite® Pro for the Smart Home A/V Kit



GripP Wire Stripper Bundle (30-10 AWG)



All-In-One UTP Snagless Crimper



CST Pro Coax Stripper 3-Level (Green Cassette: .279/.201)



BroadcastReady™ Kit