



BNC/TNC & Mini-UHF Ergonomic CrimpALL Crimper

Part number: 8007 Technical

Part numbers

Tool & Die: 8007

Die only: 2047

Description

Crimps BNC/TNC & mini-UHF 50 & 75 ohm coaxial connectors.

Type

RG59, RG62, Belden 8281 & 1505A

Crimp size

.315/.252/.068" HEX & .042" SQ

Connector style

Kings, ADC, Amphenol, etc.

Connector type

50 & 75 ohm 2- & 3-piece BNC/TNC

We also suggest



All-In-One UTP Snagless Crimper



SealTite® ProM Coax Crimper



DataReady® PRO Kit



Coax 3-Way Tool



Ultimate Coax Compression Tool Kit