



RG58 & RG59 1300 Series Crimper

Part number: 1317  Technical

Part numbers

Tool & Die: 1317

Die only: 2034

Description

Crimps 3-piece BNC/TNC coaxial connectors.

Type

RG58, RG59, RG62 AU

Crimp size

.256/.213/.068" HEX

Connector style

Common manufacturers'

Connector type

BNC/TNC



RG58 & RG59 1300 Series Crimper

Technical information

| | |
|-----------------|------------------|
| Weight | 10.4 oz. (296 g) |
| Length | 8.9" (225 mm) |
| Warranty | Lifetime |