




Electrical and Industrial > Crimpers > Die Sets - CrimpALL @/8000 & 1300 Series



Die for CrimpALL/8000 & 1300 Series Open Barrel Non-Insulated Terminal - 2033

Part number: 2033 Technical

Description

Die set for 22-10 AWG (.34-2.5 mm²) open barrel, narrow, non-insulated terminals and lugs for standard commercial terminals. Works with CrimpALL® & 1300 Series frames.

Type

22-14 AWG (.34-2.5 mm²) stranded wire

Crimp size

22-18/16-14/12-10

Connector style

Open barrel, non-insulated terminals & lugs; F-Type or B-Type

Die for CrimpALL/8000 & 1300 Series Open Barrel Non-Insulated Terminal - 2033

Technical information

Weight	2 oz.
Warranty	One-year