



Soder-Wick® Lead-Free SD

The fastest, safest desoldering braid specifically for use with lead-free applications

- Engineered specifically for high temperature, lead-free solders
- Transfers heat to the solder joint more quickly and efficiently than conventional desoldering braids
- Specifically designed for all lead-free solders
- Can also be used with Tin/Lead solders
- Soder-Wick® Lead-Free packaged in ESD-safe static dissipative bobbins
- Minimizes the risk of damage associated with static electricity
- Noncorrosive ultra high purity no-clean flux
- Will not leave ionic contamination on the boards
- Especially effective at removing residual solder from SMT pads
- RoHS Compliant



- 40-1-5** Size #1 (0.030"/0.8mm) 5 feet (1.5 m)/bobbin, 25 bobbins/bag
- 40-2-5** Size #2 (0.060"/1.5mm) 5 feet (1.5 m)/bobbin, 25 bobbins/bag
- 40-3-5** Size #3 (0.080"/2.0mm) 5 feet (1.5 m)/bobbin, 25 bobbins/bag
- 40-4-5** Size #4 (0.110"/2.8mm) 5 feet (1.5 m)/bobbin, 25 bobbins/bag
- 40-2-10** Size #2 (0.060"/1.5mm) 10 feet (3.0 m)/ bobbin, 25 bobbins/bag
- 40-3-10** Size #3 (0.080"/2.0mm) 10 feet (3.0 m)/bobbin, 25 bobbins/bag
- 40-4-10** Size #4 (0.110"/2.8mm) 10 feet (3.0 m)/bobbin, 25 bobbins/bag
- SW14025** Size #2 (0.060"/1.5mm) 5 feet (1.5 m)/bobbin, 10 bobbins/can
- SW14035** Size #3 (0.080"/2.0mm) 5 feet (1.5 m)/bobbin, 10 bobbins/can
- SW14045** Size #4 (0.110"/2.8mm) 5 feet (1.5 m)/bobbin, 10 bobbins/can



Product Selection Guide

PRODUCT	SIZE	COLOR	5' 1.5m	10' 3.0m	25' 7.5m	100' 30.5m	500' 152.5m	VACUPAK™	APPLICATION
Soder-Wick® Lead-Free SD	2	.060"/1.5mm	Yellow	40-2-5	40-2-10			SW14025	Small Pads, SMDs
	3	.080"/2.0mm	Green	40-3-5	40-3-10			SW14035	Medium Pads
	4	.110"/2.8mm	Blue	40-4-5	40-4-10			SW14045	Large Pads

© Copyright 2013 ITW Chemtronics

Adobe® Reader® is required to open PDF files.

