

<b>0359</b>	<b>0358</b>	<b>0360</b>	<b>0343</b>
<b>0359-0-15-XX-34-XX-10-0</b> Press-fit in .090 mounting hole	<b>0358-0-15-XX-34-XX-10-0</b> Press-fit in .090 mounting hole	<b>0360-0-15-XX-34-XX-10-0</b> Press-fit in .090 mounting hole	<b>0343-0-15-XX-34-XX-10-0</b> Press-fit in .090 mounting hole

<b>0356</b>	<b>6659</b>	<b>0347</b>	<b>0329</b>
<b>0356-0-15-XX-34-XX-10-0</b> Solder mount in .102 min. mounting hole Also available on 24mm wide carrier tape: 1,100 parts per 13" reel. Order as: 0356-0-57-XX-34-XX-10-0	<b>6659-0-15-XX-34-XX-10-0</b> Solder mount in .102 min. mounting hole	<b>0347-0-15-XX-34-XX-10-0</b> Solder mount in .120 min. mounting hole	<b>0329-0-15-XX-34-XX-10-0</b> Solder mount in .075 min. mounting hole. "knock out" bottom.

<b>0814</b>	<b>5059</b>	<b>8360</b>	<b>9359</b>
<b>0814-0-15-XX-34-XX-04-0</b> Solder mount in .082 min. mounting hole	<b>5059-0-15-XX-34-XX-04-0</b> Press-fit in .090 mounting hole	<b>8360-0-15-XX-34-XX-10-0</b> Press-fit in .087 mounting hole	<b>9359-0-15-XX-34-XX-10-0</b> Press-fit in .090 mounting hole

<p><b>SPECIFICATIONS</b></p> <p><b>SHELL MATERIAL:</b> Brass Alloy 360, 1/2 Hard</p> <p><b>CONTACT MATERIAL:</b> Beryllium Copper Alloy 172, HT</p> <p><b>DIMENSION IN INCHES</b> <b>TOLERANCES ON:</b> LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°</p>	<p><b>ORDER CODE: XXXX - X - 15 - XX - 34 - XX - XX - 0</b></p> <p><b>BASIC PART #</b> →</p> <p><b>SPECIFY SHELL FINISH:</b></p> <ul style="list-style-type: none"> <li>01 200μ" TIN/LEAD OVER NICKEL</li> <li>◇ 80 200μ" TIN OVER NICKEL (RoHS)</li> <li>◇ 15 10μ" GOLD OVER NICKEL (RoHS)</li> </ul> <p style="text-align: center;"><b>CONTACT</b></p> <p>#34 CONTACT (DATA ON PAGE 224)</p>	<p><b>SPECIFY CONTACT FINISH:</b></p> <ul style="list-style-type: none"> <li>01 200μ" TIN/LEAD OVER NICKEL</li> <li>◇ 80 200μ" TIN OVER NICKEL (RoHS)</li> <li>◇ 27 30μ" GOLD OVER NICKEL (RoHS)</li> </ul>
--	--	---

