

0355	0354	3490	3808
<p>0355-0-15-XX-02-XX-10-0 Solder mount in .102 min. mounting hole</p>	<p>0354-0-15-XX-02-XX-10-0 Pentagonal press-fit in .104 min. plated thru hole</p>	<p>3490-0-15-XX-02-XX-10-0 Press-fit in .091 mounting hole</p>	<p>3808-0-15-XX-02-XX-10-0 Press-fit in .090 mounting hole</p>

9184	9222		
<p>9184-0-15-XX-02-XX-40-0 Bottom entry, surface mount .092 min. plated thru hole. Also available on carrier tape, Order as: 9184-0-57-XX-02-XX-40-0</p>	<p>9222-2-15-XX-02-XX-40-0 Bottom entry, surface mount .082 min. plated thru hole. Also available on carrier tape, Order as: 9222-2-57-XX-02-XX-40-0</p>	<p>Carrier tape format for 9184 & 9222. 1,500 pieces per 13" reel</p>	

--	--	--	--

<p>SPECIFICATIONS</p> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°</p>	<p>ORDER CODE: XXXX - X - 15 - XX - 02 - XX - XX - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH:</p> <ul style="list-style-type: none"> 01 200µ" TIN/LEAD OVER NICKEL ◇ 80 200µ" TIN OVER NICKEL (RoHS) ◇ 15 10µ" GOLD OVER NICKEL (RoHS) <p style="text-align: center;">CONTACT</p> <p>#02 CONTACT (DATA ON PAGE 225)</p> <p style="text-align: center;">SPECIFY CONTACT FINISH:</p> <ul style="list-style-type: none"> 01 200µ" TIN/LEAD OVER NICKEL ◇ 80 200µ" TIN OVER NICKEL (RoHS) ◇ 27 30µ" GOLD OVER NICKEL (RoHS)
--	--

