


TCP 0,25A

Order No.: 0712123

The illustration shows version TCP 2A



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Commercial data	
EAN	4017918848422
Pack	20 Pcs.
Customs tariff	85362010
Weight/Piece	0.0111 KG
Catalog page information	Page 390 (CL-2007)

Product notes

WEEE/RoHS-compliant since:
01/01/2003



Technical data	
General	
Color	black
Insulating material	PA
Inflammability class acc. to UL 94	V0

Dimensions

Width	8.2 mm
Length	24.5 mm
Height NS 35/7,5	55 mm

Technical data

Fuse	Slow-blow
Fuse type	Automatic device
Nominal current I_N	0.25 A
Nominal voltage U_N	250 V AC 65 V DC
Switching capacity I_{CN}	(6x I_N for nominal currents 0.25 A to 4 A) (8x I_N for nominal currents 6 A to 10 A)
Ambient temperature (operation)	-20 °C ... 60 °C

Certificates / Approvals



Certification

CUL, GOST, UL, VDE-PZI

Accessories

Item	Designation	Description
------	-------------	-------------

Marking

0807180	ZBFM 5/OG:UNBEDRUCKT	Zack marker sheet, flat, unprinted: 120-section, 10 strips à 12 markers, sufficient for 120 terminal blocks, for all terminal blocks, pitch 5.2 mm, labeling with M-PEN or CMS system, color: orange
0803595	ZBFM 5/WH:UNBEDRUCKT	Zack marker sheet, flat, unprinted: 120-section, 10 strips à 12 markers, sufficient for 120 terminal blocks, for all terminal blocks, pitch 5.2 mm, labeling with M-PEN or CMS system, color: white
0803647	ZBFM 5:SO/CMS	Special printing, Zack marker sheet, flat, 120-section, divisible, marking according to customer requirements

Dimensioned drawing

