



372-2 Compact Meter



MODEL 372-2—Ohmmeter, 0.2 to 50 MΩ

Provides a wide range of resistance measurements in a small package. .2 ohm to 50 megohms. Especially useful for checking submersible pumps. Ideal for use in schools, on test benches or at incoming inspection facilities.

- **Ranges**, 0-500/ 0-5000/0-50,000/ 0-500,000 Ohms; 0-5 and 0-50 Megohms
- **Center Scale**, 5/50/500/5,000/ 50,000/500,000 Ohms
- **Accuracy**, ±3° of Linear Arc Length
- **Includes Battery and Alligator Clip Leads**



Ohms Range	Ohms Center	Maximum DC Test Current at Zero Ohms	Maximum DC Test Voltage (Open Circuit)
RX1 (0-500Ω)	50Ω	300mA	1.5V
RX10 (0-5MΩ)	50Ω	30mA	1.5V
RX100 (0-50KΩ)	500Ω	3mA	1.5V
RX1K (0-500KΩ)	5KΩ	0.3mA	1.5V
RX10K (0-5MΩ)	50KΩ	0.63mA	30V
RX100K (0-50MΩ)	500Ω	0.063mA	30V

BATTERY TYPES

- (1) 1.5 "C", NEDA 14A
- (1) 30V 'B', NEDA 210

Ordering Information

COMPACT METER	Catalog No.	ACCESSORIES	Catalog No.
372-2 Ohm meter	12311	Case, Brown Padded Polyester	00836
		Leads	00125