

ALLIGATOR CLIPS

ALLIGATOR CLIPS



A



B



C



D



E



F



G



H

PART NO.	STYLE	FIG.	MATERIAL	PLATING	LENGTH	BARREL OD	CONNECTION
300	Standard	A	Steel	Bright Tin	2	3/16	
380			Copper	Clear Chromate			
301-102	Insulated - Red	B	Steel	Bright Tin	2-7/16	3/8	Solder or Banana Plug
301-103	Insulated - Black						
381-102	Insulated - Red						
381-103	Insulated - Black						
720	Threaded 8-32	C	Steel	Bright Tin	2	3/16	Threads onto Test Prod
310	Threaded 10-32						
347	Internal Tooth						
350	Standard	E	Copper	Clear Chromate	2	3/16	Solder or Banana Plug
360							Screw, Solder or Banan Plug
351-102	Insulated - Red	D	Steel	Bright Tin	2-7/16	3/8	Solder or Banana Plug
351-103	Insulated - Black						
361-102	Insulated - Red						
361-103	Insulated - Black						
333	Standard	G	Steel	Bright Tin	2	3/16	Accepts .080" Phone Tip
338	Miniature	F	Copper	Clear Chromate	1-1/4	Forked End	Solder Connection
367							
331-102	Standard Boot	H	Rubber	Red	2	9/32	Covers Standard Clips
331-103				Black			
389-102	Miniature Boot			Red	1-3/8	7/32	Covers Miniature Clips
389-103				Black			

