

New!!


- ◆ New to the Smith selection is this retractable shrouded banana plug. It is offered as a 36" lead with a stripped end ready for your application.



289-36

- ◆ A standard gold plated banana plug is housed in a spring loaded Nylon 6/6 housing. This plug, developed for maximum safety, is available in red (-102) or black (-103.) Please add color as suffix to part number.

- ◆ All Jumpers shown here are supplied as either a pair, (one red, one black) or individually in red (-102) or black (-103). Add color as suffix to part number.



A
Standard Booted Alligator Clip to Angled Banana Plug



B
Standard Booted Alligator Clip at each end



C
Standard Booted Alligator Clip to Stacking Banana Plug



D
Standard Booted Alligator Clip to Spade Lug



E
Standard Alligator Clip to Spade Lug



F
Standard Booted Alligator Clip to Stacking Phone Tip



G
Standard Stacking Banana Plug at each end

PART NO.	FIG.	LENGTH INCHES	WIRE	INSULATION	UNIT
1332	A	48	#18 AWG	PVC	Pair
1596-12-	B	12	#18 AWG	PVC	One
1596-24-	B	24	#18 AWG	PVC	One
1596-36-	B	36	#18 AWG	PVC	One
1596-48-	B	48	#18 AWG	PVC	One
1596-60-	B	60	#18 AWG	PVC	One
629	B	12	#20 AWG	Rubber	Pair
657	B	24	#20 AWG	Rubber	Pair
658	B	36	#20 AWG	Rubber	Pair
659	B	48	#20 AWG	Rubber	Pair
1866-12-	C	12	#18 AWG	PVC	One
1866-24-	C	24	#18 AWG	PVC	One
1866-36-	C	36	#18 AWG	PVC	One
1866-48-	C	48	#18 AWG	PVC	One
1866-60-	C	60	#18 AWG	PVC	One
1867-12-	D	12	#18 AWG	PVC	One
1867-24-	D	24	#18 AWG	PVC	One
1867-36-	D	36	#18 AWG	PVC	One
1867-48-	D	48	#18 AWG	PVC	One
1867-60-	D	60	#18 AWG	PVC	One
649	E	48	#20 AWG	Rubber	Pair
1865-12-	F	12	#18 AWG	PVC	One
1865-24-	F	24	#18 AWG	PVC	One
1865-36-	F	36	#18 AWG	PVC	One
1865-48-	F	48	#18 AWG	PVC	One
1865-60-	F	60	#18 AWG	PVC	One
1510-8-	G	8	#18 AWG	PVC	One
1510-12-	G	12	#18 AWG	PVC	One
1510-24-	G	24	#18 AWG	PVC	One
1510-36-	G	36	#18 AWG	PVC	One

