



#### **PRODUCTS**

Series



**CROSS-REFERENCE** 

Print

# ightharpoons


#### Plug-in Screw Connector System for Printed Circuit Boards

3D Model

Can plug with

**TYPE 930-FL (-DS)** 

3.5 mm spacing - 2 to 24 poles



750000 EL

Download PDF

930-FL (-DS)




One possible variation of assembly



RoHS WEEE Pb free compliant

#### **Description**

- Plug
- Plug-In Direction Perpendicular to PCB and Wire Entrance Parallel to PCB when plugged with 931-SLS
- Plug-In Direction and Wire Entrance Perpendicular to PCB when plugged with 931-FST



Color specifications

### Dimensions: mm (in.)

 $Length \ of \ Connector \ (L)$   $L = \ No. \ of \ Poles \ x \ Center \ to \ Center \ Spacing$ 

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

#### **Approval Information**

How to order

UL File No.E69841 CSA File No.LR24322

Rating	Current(A)	Voltage(V)	Application group	AWG
UL	6	300	В	30-18
CSA	6	300	В	28-18

<sup>\*</sup> DS version is CSA certified for 28-20 AWG.

## **Screw Tightening Torque:**

UL: 2.0 Ifbin CSA: 0.2 Nm

Rated Impulse Withstand Voltage: 2500 V

#### Material

### **Technical Data**

Center to Center Spacing: 3.5 mm (0.138 in.)

**Nominal Cross Section:** 0.75 mm<sup>2</sup> (1162 mils<sup>2</sup>)

Wire Stripping Length: 5 mm (0.197 in.)

#### **Application**

This can be plugged with the 931-SLS. Entry of the pin can be on top side or on the bottom of these plugs. You can stack the plug on top of each other when used with extra long pins on the 931-SLS strips.

color grey Temperature limits:

**Short Time**: 140°C (284°F) Continuous: RTI 105°C (221°F)

**Low Limit**: -40°C (-40°F)

**Comparative Tracking Index:** CTI > 600

Molding: Polyamide, self extinguishing UL 94, V-0,

Oxygen Index Rating: 32%

Terminal Body: Nickel plated copper alloy

Wire Protector: Nickel silver

Contact Spring: Tin plated copper alloy

Screw: M2, Slotted head, zinc plated blue passivated,

steel substrate

Top of page

POLES:

02 to 24

How to order

Item 930-FL (-DS)

**Options** FST: 931-FST pinstrips assembled to plug

SM: Special Marking (please provide sketch)

G05: Gold Plating (5 micro inches) G30: Gold Plating (30 micro inches) S30: Silver Plating (30 micro inches)

SLS: 931-SLS Pinstrips assembled to Plug

Note: Plated component: contact spring

Ordering Note: Version with 7 mm spacing (932-FL (-DS)).

WIRE PROTECTOR:

with: - DS

Request sample Request quote

Quantity

**Accessories** 

BST Self Adhesive Marking Strips.

Consecutively numbered.

LST Single Pins.

Add to shopping cart

2008, WECO Electrical Connectors Inc.

930-FL

ISO 9001 registered quality management system