
	F	PRODUCT SEARCH	
WECO®			
PRODUCTS		CROSS-REFERENCE	

## Screw Connectors for Printed Circuit Boards

TYPE 976-T (-DS)				
7.5 mm spacing - 2 and 3 poles				
Distributor Stock Check				



## **Description**

Can be installed anywhere on PCB without wires or screws interfering with the rest of PCB. Can be located next to each other back-to-back, front-to-front and front-to-back. The screws and wire entries are easily visible, accessible and usable, an ergonomic advantage.

- Dovetail version
- Wire entrance at 45° angle to PC Board
- Can be installed anywhere on PCB without wires or screws interfering with other components
- Can be factory, field or distributor assembled to almost any length

## **Technical Data**

Center to Center Spacing: 7.5 mm (0.295 in.) Nominal Cross Section: 2.5 mm<sup>2</sup> (3874 mils<sup>2</sup>) Wire Stripping Length: 6.5 mm (0.26 in.) **Recommended Hole Diameter in PC Board:** 1.3 mm (0.051 in.)

UL File No.E69841 👊 CSA File No.LR24322

**Approval Information** 

Rating	Current(A)	Voltage(V)	Application group	AWG
UL	15	300	B,C	26-12
CSA	15	300	B,D,E	22-10

\* Version DS is CSA certified for 26-10 AWG. UL: 24-26 AWG range for factory wiring only.

Screw Tightening Torque: UL: 4.5 Ifbin CSA: 0.51 Nm International Approvals:



Rated Impulse Withstand Voltage: 6000 V

Material

	Top of page	Molding: Polyamide, self extinguishing UL 94, V-0, color grey Temperature limits: Short Time: 140°C (284°F) Continuous: RTI 105°C (221°F) Low Limit: -40°C (-40°F) Comparative Tracking Index: CTI > 600 Oxygen Index Rating: 32% Terminal Body: Tin plated copper alloy Wire Protector: Tin plated copper alloy Wire Protector: Tin plated copper alloy Screw: M3, Slotted head, zinc plated clear passivated, steel substrate Solder Pin: Ø 1.0 mm (0.04 in.), Tin plated copper alloy
How to	order	
tem	976-T (-DS)	Request sample
Options	CN: Consecutive Numbering (hot stamped numbers)	Request quote
	SM: Special Marking (please provide sketch)	
	G05: Gold Plating (5 micro inches)	Quantity

Protruding length of pins, in millimeters:

1

**Note:** Plated component: terminal body

WIRE PROTECTOR: with: - DS

G30: Gold Plating (30 micro inches)

S30: Silver Plating (30 micro inches)

BS: Copper Alloy Screw

XXMM: Longer solder Pins up to 75 mm (3 in.)

POLES: 02 and 03

Add to shopping cart

BST Self Adhesive Marking Strips.

Consecutively numbered.

2008, WECO Electrical Connectors Inc.

976-T

ISO 9001 registered quality management system

Accessories