9.25" OPENING 11.25" 07450 SHEET PROTECTOR

Description:

This product is designed for use in ESD controlled areas where there are ESD sensitive devices. All sheet protectors are made from a stable, amine-free, coextruded polyolefin clear film 3 Mil thick film. Dissipative agent is extruded in and is slow blooming with an effective shelf life in excess of two years. It can be cleaned for use in Class 100 Clean Rooms. This product is designed to hold 8 1/2" x 11" sheets and meets or exceeds the requirements of MIL-B-81705C, Type II.

Humidity independent. N-Octanoic Acid Free. Does not promote corrosion. Has no measurable outgassing.

Electrical Properties:

Static Decay: < 1.0 sec. per FTMS 101C, Method 4046 Surface Resistivity: 10¹¹ Ohms/sq. per ASTM D-257
Triboelectric Charge Generation: Negligible per EIA-541

Specifications:

Polycarbonate Compatibility: 3,400 PSI @ 73°F

Corrosivity: Negligible per FTMS 101C-3005 Tensile Strenath: 2000-3000 PSI per ASTM D-882 Elongation @ Break: 500-800% per ASTM D882 Ball Burst Impact Strength: 20-30 cm/kg per ASTM D-3420 Tear Propagation: 200 grams per ASTM D-1938 Modulus of Elasticity: 10,000-15,000 PSI per ASTM D-882A Coefficient of Friction: 0.3 Kinetic, Film to Film per ASTM D-1894

A. Sheet Protectors are hot stamped with:

"STATIC SAFE DESCO INDUSTRIES ITEM #07450"

SHEET PROTECTOR, STATIC DISSIPATIVE, 3 MIL

DESCO

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: www.desco.com PHONE (909) 627-8178 FAX (909) 627-7449

DESCO EAST: 90 HUDSON RD, CANTON, MA 02021-1407 PHONE (781) 821-8370 FAX (781) 575-0172

DRAWING NUMBER 07450 **DATE**: 3/05