

See reverse side for item numbers and descriptions.

Description:

Anti-fatigue conductive floor mat; homogeneous vinyl laminated to a unique super-resilient, double-thick, rubber foam base. This conductive diamond plate surface offers a high-tech look while providing traction. The diamond plate surface and tapered edges are adopted from industrial safety applications; it is a proven safety and anti-fatigue product. The yellow safety border provides high visibility and can alert employees to ESD controlled areas.

Statfree DPL $Plus^{TM}$ meets the technical range recommended in ANSI/ESD S20.20 for ESD Floor < 1 x 10E9 ohms tested per ANSI/ESD S7.1. Being a conductive floor mat, Statfree DPL $Plus^{TM}$ is suitable as the ESD floor component in a Flooring - Footwear System, ANSI/ESD S20.20 recommended technical requirement of <3.5 x 10E7ohms tested per ESD STM 97.1.

Specifications:

Construction: Homogenous vinyl laminated to dual-layer foam rubber

Thickness: 0.450" (11.4mm)

Surface: Embossed Diamond Plate Design

Hardness: 90 Shore A

Heat Resistance: 0°F to 150°F continuous
Weight: 1.45 lbs. per square foot
Density: Average: 33 lbs. per cubic foot

Grounding

This material must be properly grounded to remove electrostatic charges to ground. Ask for Technical Bulletin TB-2000 for mat grounding instructions.

Grounding Intervals for ESD Mats

Sufficient ground cords should be used to reliably meet ANSI/ESD S20.20 Table 1 less than 1 x 10E9 ohms for worksurfaces. An industry recommendation has been that continuous runs of ESD matting should be grounded at ten-foot intervals to allow proper charge decay rates with each individual ESD mat should be grounded with ground snap located no further than five feet from either end.

Cleaning

For optimum electrical performance, surface must be cleaned regularly using an ESD mat cleaner. We suggest using our Reztore™ Surface & Mat Cleaner Item #10435 or Static Wipes Item #10600. Do not use cleaners with silicone. Silicone buildup will create an insulative film on the surface.

Electrical Properties:

<u>Property</u> <u>Test Method</u> <u>Value</u>

Charge Decay: FTMS 101C, Method 4046 5,000 volts-0 volts in 0.03 seconds

RTT Resistance: ANSI/ESD S7.1 10E3 - 10E5 ohms RTG Resistance: ANSI/ESD S7.1 10E3 - 10E5 ohms

Electrical Properties obtained by testing to industrial standards by an independent testing laboratory @ 100 Volts and 50% relative humidity unless otherwise specified. Complete text of the test report is available upon request.





STATFREE DPL *PLUS*™ FLOOR MAT, VINYL, CONDUCTIVE, ANTI-FATIGUE



DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: Desco.com PHONE (909) 627-8178 FAX (909) 627-7449

DESCO EAST: 90 HUDSON RD, CANTON, MA 02021-1407 PHONE (781) 821-8370 FAX (781) 575-0172 DRAWING NUMBER PM-125 DATE: November 2007 Matting materials have a tendency to shrink slightly when first unrolled. In applications where length is critical, allow the material to relax for at least 4 hours before cutting to size. Always trim with a sharp knife or razor blade.

Disclaimer:

All statements, technical data, and recommendations contained herein are based upon tests we believe to be reliable. However, the accuracy or completeness thereof is not guaranteed. The proper and correct applications of products and data is the responsibility of the user. Statements or recommendations not contained herein shall have no force or effect unless embodied in a written agreement signed by authorized offers of Desco Industries, Inc.

Look for the Statfree[®] brand on Desco ESD matting. Statfree DPL *Plus™* Floor Mats are permanently marked for your protection and auditing purposes.



RoHS Compliance Statement

None of the following materials are intentionally added in manufacturing this product: lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB) or polybrominated diphenyl ethers (PBDE) as outlined in the Directive 2002/95/EC Article 4.1. See Desco Industries Inc. letter on-line at Desco.com.

Limited Lifetime Warranty

Desco warrants for one year that Statfree[®] matting products will be free of defects in materials and workmanship and will guarantee dissipative/ conductive mat properties for the life of the mat. Damage to matting caused by misuse of any kind, including using inappropriate cleaners is not covered by Desco Limited Warranty.

Item No.	Size	Thickness
40979 Floor Mat	24" x 36"	0.450"
40980 Floor Mat	36" x 48"	0.450"
40981 Floor Mat	36" x 60"	0.450"
40982 Floor Runner	36" x 60'	0.450"

Mats include our complete Floor Ground Kit Item #14234. Rolls do not include hardware.

Tolerances:

Width ± .250"

Length ± .250" every 1 linear foot of running material.