

19492 - METER, STATIC FIELD, DIGITAL



Technical Documents

TB-3040 - Digital Static Field Meter

Features And Benefits

- Portable Meter for Testing of Electrostatic Fields
 Measures surface voltage and polarity on objects up to ±19.99 kV at a distance of 1 inch
- Durable Dissipative Housing Design with Membrane Switches (NEW)
 Protects meter from physical damage and minimizes wear.
- LED Range Finder

 Red ranging lights help operator to place the meter at the correct distance from the
- Hold Button

object being measured

Allows the measurements to be retained for easy reading, and extends battery life

- NIST Calibrated with Certificate
 Calibrated with accepted procedures and standards traceable to the National Institute of Standards and Technology. For more information on calibration of Desco products, see Calibration
- Made in America

This item is made and stocked in **Chino**, **CA**

Estimated Shipping Weight: 0.58 Pounds

Additional Accessories:

- Conductive Plate
 - 19441 Conductive Plate to measure the offset voltage and discharge times of air ionizers
- Human Body Model (HBM) Test Fixture
 19448 Personal HBM Test Fixture to approximate electrical charges generated on the human body while walking or moving
- Test Kit Upgrade
 19440 Test Kit Upgrade includes Charger and Conductive Plate