
Switchcraft®

Previous Page | Return to Index | Next Page



3.5 mm DUAL STEREO JACK

- 1. UNSHIELDED 35RAPC7J
- 2. UNSHIELDED 35RAPC7J
- 3. SHIELDED 35RAPC7JS

click here to download a schematic drawing

(you will need to have Adobe Acrobat installed on your system to do this)



FEATURES

- * 3-conductor, miniature phone jack mates with 3.5 mm finger plugs.
- * Saves board space...two jacks in a single vertical mount footprint.
- * Ideally suited for infra-red and convection oven soldering 235°C (455°F).
- * Board retention pins accommodate PC board thickness range of .050 inches to .080 inches.
- * Single-screw panel mounting hole is standard.
- * EMI-RFI shield, optional.
- * Housing UL 94V-0 rated against flammability.

APPLICATIONS

- * Multi-media workstations
- * Headphones/microphone sets
- * Interactive TV
- * Audio
- * Telecommunications
- * Medical
- * Computer
- * Instrumentation

MATERIALS

Housing: Thermoplastic.

Tip and Ring Springs: Silver-plated copper alloy.

Shunt Terminals: Silver-plated copper alloy.

Sleeve Terminals: Silver-plated copper alloy.

Shield: Pre-tinned copper alloy.

PERFORMANCE SPECIFICATIONS

- 1. **Insertion/Extraction Forces, initial:** 0.8 to 6 pounds.
- 2. Dielectric Withstanding Voltage: 500 VAC.
- 3. **Insulation Resistance, initial:** 100 Megaohms, min.
- 4. Contact Resistance: Between plug and jack:
- 50 milliohms, maximum Between springs and shunts:
- 30 milliohms, maximum.
- 5. Life: 5000 cycles, minimum.

ORDERING INFORMATION

Part Number:

Shielded - 35RAPC7JS

Unshielded - 35RAPC7J

- **1.** Order by part number.
- 2. Contact Switchcraft for special order information.

Previous Page | Return to Index | Next Page


To search a category please click on the corresponding icon:


Switchcraft

ONLINE CATALOG

SWITCHCRAFT, INC. 5555 N. Elston Ave. Chicago, IL 60630 • 773 792-2700 • FAX: 773 792-2129 www.switchcraft.com

3.5 mm DUAL STEREO JACK





0. 16 0. 0. 06 (1.5) 0. 30 (7.5) 0. 20 (5.0) 0. 57 (14.6) 0. 66 (1.5) 0. 20 (5.0) 0. 20 (5

NOTES:

- 1. Shield isolated from terminals 1 and 6.
- 2. Width of all terminals = 0.032" (0.814mm).
- 3. Use Camcar Textron S25 T8 TORX pan head "Duro-PT" thread cutting fastener of appropriate length or equivalent.