
Switchcraft®

Previous Page | Return to Index | Next Page











RASM742TR



RASM752TR

Sub-miniature Power Jacks

Switchcraft introduces a new series of sub-miniature power jacks. These sub-miniature power jacks feature ultra-compact housings and pin diameters as small as 0.65mm. Available in PC mount and true surface mount, with other options including open frame and shielded versions. All SMT versions come on tape and reel. Contact Switchcraft for exact reel dimensions.

Features and Benefits

- SMT mounting
- Tape and reel packaging
- Wide variety of circuits

Applications

- Computer
- Video Cameras
- Personal/Portable Audio Devices
- Multimedia

Specifications

Material:

• Housing: Black nylon

• Sleeve, Ring and Tip Terminals: Tin, Silver-plated

• Shunt Terminal: Brass, Silver-plated

Electrical:

• Current Rating: 3A

• Contact Resistance: <50 mohms

• Insulation Resistance: 100 mohms (min.)

• Dielectric Withstanding Voltage: 250VAC @ 1 minute

Mechanical:

• Lifecyles: 5,000

• Operating Temperture: -25°C to +85°C


Ordering Information


Part Number	Description
RAPC742	PC mount, 1mm pin
RASM742TR	SMT mount, 1mm pin
RAPC732OF	Open frame, PC mount, 1.3mm pin
RAPC742OF	Open frame, PC mount, 1mm pin
RAPC752	PC mount, 0.65mm pin
RAPC752S	Shielded, PC mount, 0.65mm pin
RASM752TR	SMT mount, 0.65mm pin
RASM752STR	Shielded, SMT mount, 0.65mm pin

Download Product Bulletin Pages:



- NPB 547a General info, photo, part numbers
- NPB 547b Schematic drawings
- NPB 547c Schematic drawings
- NPB 547d PC board layouts





JACKS AND PLUGS

Subminiature Power Jacks

Switchcraft introduces a new series of sub-miniature power jacks. These sub-miniature power jacks feature ultra-compact housings and pin diameters as small as 0.65mm. Available in PC mount and true surface mount, with other options including open frame and shielded versions. All SMT versions come on tape and reel. Contact Switchcraft for exact reel dimensions.

Features and Benefits

- SMT mounting
- Tape and reel packaging
- Wide variety of circuits

Applications

- Computer
- Video Cameras
- Personal/Portable Audio Devices
- Multimedia

Specifications

Material

Housing: Black nylon

Sleeve, ring, and tip terminals: Tin, silver-plated

Shunt terminal: Brass, sliver-plated

Electrical

Current Rating: 3A

Contact Resistance: <50 mohms

Insulation Resistance: 100 mohms (min.)

Dielectric Withstanding Voltage: 250VAC@ 1 minute

Mechanical

Lifecycles: 5,000

Operating Temperature: -25 to +85 C

Ordering Information

Part Number **Description** RAPC742 PC mount, 1mm pin RASM742TR SMT mount, 1mm pin RAPC732OF Open frame, PC mount, 1.3mm pin RAPC742OF Open frame, PC mount, 1mm pin RAPC752 PC mount, 0.65mm pin RAPC752S Shielded, PC mount, 0.65mm pin RASM752TR SMT mount, 0.65mm pin RASM752STR Shielded, SMT mount, 0.65mm pin

PRODUCT BULLETIN **547**



