




Home About Us Products Applications Sales Support Contact Us Search

[Industrial Products](#) > [Industrial Switches](#) > [Pendant Nurse Call Cord Switches](#)



enlarge

Pendant Nurse Call Cord Switches

Momentary cord (pendant) switches can be specified with red or black pushbuttons, 1-C switching, solder terminals and metal handle (Series E900), plastic handle (Series EP900), or metal handle with clamp and strain relief (Series ED900).

Products

Specifications

Need more info? Contact Switchcraft customer service

[Printer friendly version](#)

SPECIFICATIONS 921 and 921K - Molded gray plastic with contrasting trim and black pushbutton.
Switch Contacts: Integral copper alloy, plated, form 1-A, 0.5 A, 50 W maximum, AC, non-inductive load. Not recommended for high voltage circuits.
Insulation: Thermoplastic UL 94V-0.
Phono Jack Terminations: (921): Standard phono jack, similar to 3501FP (see Jacks and Plugs Section).

PART NUMBERS

Part Number	Description
921	Cordette switch, phono jack termination.
921K	Same as 921, except with 6 foot (1.8 meter), 2-conductor cable with stripped and tinned leads.

SPECIFICATIONS SERIES E900, EP900:

Housing: Series E900 - Copper alloy, plated. Series EP900 - Molded black plastic.

Switch Bushing: Copper alloy, plated.

Insulation: Rigid plastic.

SERIES ED900:

Housing: Die-cast zinc, plated.

Switch Body and Insert Bushing: Copper alloy, plated.

Insulation: Rigid plastic.

Cable Relief Bushing: Black thermoplastic rubber.

Pressure Plates: Stainless steel.

Cable Relief Screws: Steel, plated.

PART NUMBERS (examples)

Pushbutton Color/Part Number		Maximum Cable Outside Diameter	Circuit
Red	Black		
E903	E913	.375" [9.5 mm]	1-C
ED903	ED913	.375" [9.5 mm]	
EP903	EP913	.250" [6.4 mm]	

5555 N Elston Ave • Chicago • Illinois • 60630 • USA • 1.773.792.2700

Home About Us Sales Contact Us Login



