

[Home](#) > [DEMO/PRODUCT DISPLAY CASES](#) >

2207 MEDIUM-DUTY ABS CASE



Colors Available: BLACK

Product Code: 2207

Description

Modern look of heavy duty grained ABS with extruded aluminum frame, deluxe golf grip handle, cast chrome key locks and piano hinge. Case comes with our standard pick-n-pluck cubed foam.

Technical Specs

- Interior Dimensions (L x W x D): 22" x 16" x 7"
- Body Depth: 4"
- Shipping Dimensions (L x W x D): 23" x 19" x 8"
- Shipping Weight: 10.30 lbs.

Blow Molded Cases



Blow Molded Cases

Meet Platt's low cost solution to "Make-Your-Own" case needs.

These cases are foam-filled and manufactured from prime, high-density polyethylene, with double wall construction. The textured exteriors resist dents, cracking and scuffs. The shells are unaffected by extreme temperatures.

The hardware features mechanical latches that are field replaceable and a mechanical hinge system that is made to last.

All cases meet U.S. 94B Specifications as an electrical insulator and are impervious to chemical attack.

Platt#	Inside Dim.			Outside Dim.		
	L	W	D	L	W	D
102	5 5/8"	3 5/8"	1 3/8"	6 1/2"	4 1/2"	1 11/16"
103	5 3/8"	3 3/8"	1 7/8"	6 1/2"	4 1/2"	2 1/8"
104	7 1/8"	4"	1 7/16"	8"	5"	1 3/4"
105	7 1/8"	4"	1 15/16"	8"	5"	2 1/8"
106	7 1/2"	5"	1 11/16"	8 1/2"	6"	2"
107	7 1/2"	5"	2 3/16"	8 1/2"	6"	2 1/2"
108	7 1/2"	5"	2 11/16"	8 1/2"	6"	3"
202	8 1/2"	5 1/2"	1 11/16"	9 1/2"	6 1/2"	2"
203	8 1/2"	5 1/2"	2 11/16"	9 1/2"	6 1/2"	2 1/2"
204	8 1/2"	5 1/2"	2 11/16"	9 1/2"	6 1/2"	3"
205	8 1/2"	5 1/2"	3 3/16"	9 1/2"	6 1/2"	3 1/2"
206	9 1/2"	6"	1 15/16"	10 1/2"	7"	2 1/16"
207	9 1/2"	6"	2 11/16"	10 1/2"	7"	3"
208	9 1/2"	6"	3 7/16"	9 1/2"	7"	3 3/4"
302	10 3/16"	6 1/2"	1 15/16"	11 3/16"	7 1/2"	2 1/4"
303	10 3/16"	6 1/2"	2 11/16"	11 3/16"	7 1/2"	3"
304	10 3/16"	6 1/2"	3 7/16"	11 3/16"	7 1/2"	3 3/4"
305	11"	7"	1 15/16"	12"	8"	2 1/4"
306	11"	7"	2 11/16"	12"	8"	3"
307	11"	7"	3 7/16"	12"	8"	3 3/4"
308	12 3/8"	6 7/8"	2 7/8"	13 1/2"	8"	3 1/4"
309	12 3/8"	6 7/8"	4 1/16"	13 1/2"	8"	4 3/8"
310	12 3/8"	6 7/8"	5 1/16"	13 1/2"	8"	5 1/2"
402	12 3/8"	7 7/8"	2 7/8"	13 1/2"	9"	3 1/4"
403	12 3/8"	7 7/8"	4"	13 1/2"	9"	4 3/8"
404	12 3/8"	7 7/8"	5 1/8"	13 1/2"	9"	5 1/2"
405	12 3/8"	8 7/8"	2 7/8"	13 1/2"	10"	3 1/4"
406	12 3/8"	8 7/8"	4"	13 1/2"	10"	4 3/8"
407	12 3/8"	8 7/8"	5 1/8"	13 1/2"	10"	5 1/2"
503	13 7/8"	8 7/8"	2 7/8"	15"	10"	3 1/4"
504	13 7/8"	8 7/8"	4"	15"	10"	4 3/8"
505	13 7/8"	8 7/8"	5 1/8"	15"	10"	5 1/2"
506	13 7/8"	9 7/8"	2 7/8"	15"	11"	3 1/4"
507	13 7/8"	9 7/8"	4"	15"	11"	4 3/8"
508	13 7/8"	9 7/8"	5 1/8"	15"	11"	5 1/2"
604	14 7/8"	10 3/8"	2 7/8"	16"	11 1/2"	3 1/4"
605	14 7/8"	10 3/8"	4"	16"	11 1/2"	4 3/8"
606	14 7/8"	10 3/8"	5 1/8"	16"	11 1/2"	5 1/2"
607	15 7/8"	10 7/8"	2 7/8"	17"	12"	3 1/4"
608	15 7/8"	10 7/8"	4"	17"	12"	4 3/8"
609	15 7/8"	10 7/8"	5 1/8"	17"	12"	5 1/2"
610	16 7/8"	11 11/16"	3 7/8"	18"	13"	4 1/4"
611	16 7/8"	11 11/16"	5"	18"	13"	5 3/8"
612	16 7/8"	11 11/16"	6 1/8"	18"	13"	6 1/2"
705	17 7/8"	12 11/16"	4 3/8"	19"	14"	4 3/4"
706	17 7/8"	12 3/4"	5 3/4"	19"	14"	6 1/4"
707	17 7/8"	12 3/4"	7 1/8"	19"	14"	7 1/2"
802*	21 5/16"	14 5/16"	6 5/8"	23"	16"	7"
803*	21 5/16"	14 5/16"	9 5/8"	23"	16"	10"
902*	25 13/16"	14 5/16"	6 5/8"	27 1/2"	16"	7"
903*	25 13/16"	14 5/16"	9 5/8"	27 1/2"	16"	10"

* Molded-in handle reduces "W" dimension usable space. Please contact Platt Engineering for info

Light-Duty ABS Cases



Light-Duty ABS Cases

This series has been a mainstay of Platt's rugged case line for over 25 years. Light-duty, black, scuff resistant molded ABS thermoplastic forms the tough shell of these cases. Foam-filled, extruded aluminum rim, drawbolt key locks and strong molded handle.

* 1425 has a medium-duty valance

Platt#	Inside Dim.			Body Depth
	L	W	D	
1410	10"	7"	5"	3"
1412	12"	8"	5"	3"
1414	12"	11"	5"	3"
1416	16"	12"	5"	3"
1426	16"	12"	7"	4"
1705	17"	11"	5"	3"
1419	18"	13"	5"	3"
1425*	18"	13"	7"	4"

Medium-Duty ABS Cases



Medium-Duty ABS Cases

Modern look of heavy-duty grained ABS with extruded aluminum frame, these foam-filled cases have a deluxe golf grip handle, cast chrome key locks and piano hinge.

* 2005 has a light-duty valance.

Platt#	Inside Dim.			Body Depth
	L	W	D	
2005*	20"	14"	5"	3"
2007	20"	14"	7"	4"
2207	22"	16"	7"	4"
2407	24"	18"	7"	4"
2807	28"	20"	7"	4"

Parallel Rib Cases



Heavy-Duty Polyethylene Cases With Stylish Parallel Rib Pattern Without Foam

The exterior shell is tough impact-resistant HMW polyethylene. Heavy-duty aluminum rim with gasket, black trim, molded handle, full-length piano hinge and cast chrome key locks.

ALL PARALLEL RIB CASES FURNISHED WITHOUT FOAM.

Platt#	Inside Dim.			Body Depth
	L	W	D	
141106PR	14 1/8"	10 1/2"	6"	3 1/2"
171206PR	17 1/4"	12 1/2"	6"	3 1/2"
201675PR	19 3/4"	15 3/4"	7 1/2"	4 1/2"
221006PR	22"	10"	6"	3 1/2"
241609PR	23 3/4"	15 3/4"	9"	4 1/2"
251709PR	25"	16 3/4"	9"	4 3/4"