

[Home](#) > [WATERTIGHT CASES](#) >

1450 CASE



EQUIPMENT
NOT INCLUDED

**Colors Available:
BLACK,SILVER,
ORANGE,
YELLOW,OD
GREEN,
DESERT TAN**

*Product Code:
1450*

Description

- Watertight, crushproof, and dust proof
- Easy open Double Throw latches
- Open cell core with solid wall design - strong, light weight O-ring seal
- Automatic Pressure Equalization Valve
- Comfortable rubber over-molded handle
- Stainless steel hardware and padlock protectors
- Pick 'N' Pluck™ with convoluted lid foam
- Personalized nameplate service available
- Unconditional Lifetime Guarantee of Excellence

Technical Specs

- Exterior Dimensions (L x W x D): 16 x 13 x 6 7/8
- Interior Dimensions (L x W x D): 14 5/8 x 10 1/8 x 6
- Weight With Foam: 6.39 lbs.
- Weight Without Foam: 5.51 lbs.
- Shipping Dimensions (L x W x D): 17" x 14" x 7"
- Shipping Weight: 9.33 lbs.

Pelican Watertight Cases



New & Improved Latches.

- 1120 Guard Box®
- 1150 Case™
- 1200 Case™
- 1300 Case™
- 1400 Case™
- 1450 Case™
- 1470 Case™
- 1470 Case™
- 1490 Case™
- 1500 Case™
- 1520 Case™
- 1550 Case™
- 1600 Case™
- 1620 Case™
- 1650 Case™
- 1700 Travel VaultIII®
- 1750 Travel Vault®



Platt#	Inside Dim.			Outside Dim.			Ship Weight
	L	W	D	L	W	D	
0350	20"	20"	18 ¹ / ₄ "	22 ¹ / ₂ "	22 ¹ / ₁₆ "	21 ¹ / ₄ "	26 lbs.
0370	24 ¹ / ₄ "	24"	23"	25 ¹ / ₄ "	26 ¹ / ₂ "	26 ¹ / ₂ "	30 lbs.
1010	4 ⁵ / ₁₆ "	2 ¹³ / ₁₆ "	1 ⁵ / ₈ "	5 ⁷ / ₁₆ "	4 ¹ / ₁₆ "	2 ¹ / ₈ "	3.2 lbs.
1020	5 ¹ / ₄ "	3 ¹ / ₂ "	1 ⁵ / ₈ "	6 ³ / ₈ "	4 ³ / ₄ "	2 ¹ / ₈ "	4 lbs.
1030	6 ³ / ₈ "	2 ⁵ / ₈ "	2"	7 ¹ / ₂ "	3 ⁷ / ₈ "	2 ⁷ / ₁₆ "	4.24 lbs.
1040	6 ⁷ / ₁₆ "	3 ¹³ / ₁₆ "	1 ¹¹ / ₁₆ "	7 ¹ / ₂ "	5 ¹ / ₁₆ "	2 ¹ / ₈ "	4.85 lbs.
1050	6 ⁷ / ₁₆ "	3 ¹³ / ₁₆ "	2 ¹¹ / ₁₆ "	7 ¹ / ₂ "	5 ¹ / ₁₆ "	3 ¹ / ₈ "	6.4 lbs.
1060	8 ⁵ / ₁₆ "	4 ⁵ / ₁₆ "	2 ³ / ₁₆ "	9 ³ / ₈ "	5 ⁹ / ₁₆ "	2 ⁵ / ₈ "	6.88 lbs.
1120WF	7 ³ / ₈ "	4 ⁷ / ₈ "	3 ¹ / ₁₆ "	8 ¹ / ₄ "	6 ⁷ / ₁₆ "	3 ⁹ / ₁₆ "	11.2 lbs.
1150WF	8 ³ / ₈ "	5 ⁷ / ₈ "	3 ⁹ / ₁₆ "	9 ¹ / ₄ "	7 ⁹ / ₁₆ "	4 ³ / ₈ "	2.5 lbs.
1200WF	9 ³ / ₈ "	7 ¹ / ₄ "	4 ¹ / ₁₆ "	10 ⁵ / ₈ "	9 ¹¹ / ₁₆ "	4 ⁷ / ₈ "	3 lbs.
1300WF	9 ³ / ₈ "	7 ¹ / ₄ "	6 ¹ / ₈ "	10 ⁵ / ₈ "	9 ¹¹ / ₁₆ "	6 ⁷ / ₈ "	3.5 lbs.
1400WF	12"	9 ¹ / ₁₆ "	5 ³ / ₁₆ "	13 ³ / ₈ "	11 ⁵ / ₈ "	6"	5.5 lbs.
1420WF	13"	5"	10"	15"	8 ¹ / ₂ "	10 ¹ / ₂ "	5.5 lbs.
1450WF	14 ¹³ / ₁₆ "	10 ³ / ₈ "	6"	16"	13"	6 ⁷ / ₈ "	7.5 lbs.
1470WF	15 ⁵ / ₄ "	10 ⁹ / ₁₆ "	3 ³ / ₄ "	16 ¹¹ / ₁₆ "	13 ¹ / ₁₆ "	4 ³ / ₈ "	7.8 lbs.
1470CC#1	15 ³ / ₄ "	10 ⁹ / ₁₆ "	3 ³ / ₄ "	16 ¹¹ / ₁₆ "	13 ¹ / ₁₆ "	4 ³ / ₈ "	6.8 lbs.
1470CC#2	15 ³ / ₄ "	10 ⁹ / ₁₆ "	3 ³ / ₄ "	16 ¹¹ / ₁₆ "	13 ¹ / ₁₆ "	4 ³ / ₈ "	6.75 lbs.
1470AC	15 ⁵ / ₄ "	10 ⁹ / ₁₆ "	3 ³ / ₄ "	16 ¹¹ / ₁₆ "	13 ¹ / ₁₆ "	4 ³ / ₈ "	6.75 lbs.
1490WF	17 ⁷ / ₈ "	11 ¹ / ₂ "	4 ¹ / ₈ "	19 ⁷ / ₁₆ "	13 ¹⁵ / ₁₆ "	4 ¹¹ / ₁₆ "	6.5 lbs.
1490CC#1	17 ⁷ / ₈ "	11 ¹ / ₂ "	4 ¹ / ₂ "	19 ⁷ / ₁₆ "	13 ¹⁵ / ₁₆ "	4 ¹¹ / ₁₆ "	8.3 lbs.
1490CC#2	17 ⁷ / ₈ "	11 ¹ / ₂ "	4 ¹ / ₂ "	19 ⁷ / ₁₆ "	13 ¹⁵ / ₁₆ "	4 ¹¹ / ₁₆ "	8.25 lbs.
1490AC	17 ⁷ / ₈ "	11 ¹ / ₂ "	4 ¹ / ₈ "	19 ⁷ / ₁₆ "	13 ¹⁵ / ₁₆ "	4 ¹¹ / ₁₆ "	8.25 lbs.
1500WF	17"	11 ⁷ / ₁₆ "	6 ¹ / ₈ "	18 ¹ / ₂ "	14 ¹ / ₁₆ "	6 ⁷ / ₈ "	8.85 lbs.
1504*	17"	11 ⁷ / ₁₆ "	6 ¹ / ₈ "	18 ¹ / ₂ "	14 ¹ / ₁₆ "	6 ⁷ / ₈ "	8.85 lbs.
1510	20 ³ / ₁₆ "	11 ³ / ₈ "	7 ¹ / ₂ "	22"	14"	9"	13.9 lbs.
1520WF	17 ⁷ / ₈ "	12 ³ / ₄ "	6 ³ / ₄ "	19 ¹ / ₈ "	15 ⁷ / ₁₆ "	7 ⁹ / ₁₆ "	10.75 lbs.
1524*	17 ⁷ / ₈ "	12 ³ / ₄ "	6 ³ / ₄ "	19 ¹ / ₈ "	15 ⁷ / ₁₆ "	7 ⁹ / ₁₆ "	10.75 lbs.
1526**	17 ⁷ / ₈ "	12 ³ / ₄ "	6 ³ / ₄ "	19 ¹ / ₈ "	15 ⁷ / ₁₆ "	7 ⁹ / ₁₆ "	10.75 lbs.
1527+	17 ³ / ₄ "	13 ¹ / ₂ "	7 ¹ / ₄ "	19 ¹ / ₈ "	15 ⁷ / ₁₆ "	7 ⁹ / ₁₆ "	10.75 lbs.
1550WF	18 ³ / ₄ "	14 ³ / ₈ "	7 ³ / ₈ "	20 ³ / ₈ "	16 ⁷ / ₈ "	8 ³ / ₈ "	13.5 lbs.
1600WF	21 ³ / ₄ "	16 ¹³ / ₁₆ "	7 ⁷ / ₈ "	24 ¹ / ₄ "	19 ⁷ / ₁₆ "	8 ¹¹ / ₁₆ "	16 lbs.
1610WF	22 ³ / ₁₆ "	17 ¹ / ₈ "	10 ⁹ / ₁₆ "	24 ⁹ / ₁₆ "	19 ⁵ / ₁₆ "	11 ¹⁵ / ₁₆ "	25.5 lbs.
1620WF	22 ⁷ / ₁₆ "	17"	12 ⁹ / ₁₆ "	24 ¹³ / ₁₆ "	19 ³ / ₈ "	13 ⁷ / ₈ "	27 lbs.
1650WF	29"	17 ⁷ / ₈ "	10 ¹ / ₂ "	32 ³ / ₄ "	20 ¹ / ₂ "	11 ⁵ / ₁₆ "	30 lbs.
1660WF	29 ¹ / ₈ "	20 ¹¹ / ₁₆ "	17 ⁵ / ₈ "	31 ¹ / ₂ "	22 ⁷ / ₈ "	18 ⁷ / ₈ "	49 lbs.
1700WF	35 ⁵ / ₄ "	13 ¹³ / ₁₆ "	5 ¹ / ₄ "	31 ¹ / ₈ "	17 ¹³ / ₁₆ "	6 ¹ / ₈ "	19 lbs.
1720WF	42"	13 ¹ / ₂ "	5 ¹ / ₄ "	44 ³ / ₈ "	16"	6 ¹ / ₈ "	21.15 lbs.
1750WF	50 ¹ / ₂ "	13 ⁷ / ₁₆ "	5 ¹ / ₄ "	53"	17 ⁷ / ₁₆ "	6 ¹ / ₁₆ "	25.65 lbs.

Pelican Protector® Watertight Equipment Cases

Watertight and airtight to 30 feet for the ultimate in protection. Constructed of light-weight space-age structural resin with a neoprene O-ring seal and exclusive purge valve. Supplied complete with pre-scored pick-n-pluck foam or padded dividers (no cutting required). Also includes locking flanges, massive multiple latches for absolute security and a comfortable molded fold-down handle. Custom colors and foam inserts fabricated on special order.

#1700 and #1750 supplied with regular foam. Pick-n-pluck is not available.

*Case With Padded Dividers **Case With Travel Bag +Travel Bag Only

Pelican Flashlights

PELICAN® FLASHLIGHTS

Platt carries a complete line of Pelican® Flashlights. Please call Platt



1900C



2400C

PELICAN® 100% GUARANTEE

Unconditional lifetime guarantee of excellence by Pelican® Products, Inc.

Pelican Tool Case



Platt#	Inside Dim.		
	L	W	D
1520T-CB	17 ⁷ / ₈ "	12 ³ / ₄ "	6 ³ / ₄ "

PELICAN® FEATURES

Pelican protector case is now available as a Platt tool case. This case is constructed of high impact co-polymer resin with a pressure relief valve and padlock loops. Meets MIL-STD 4150 for stacking, drop test and chemical attack.

This case is not watertight.