

[Home](#) > [WATERTIGHT CASES](#) >

1550 CASE



EQUIPMENT  
NOT INCLUDED

**Colors  
Available:  
BLACK,  
SILVER,  
ORANGE,  
YELLOW,OD  
GREEN,  
DESERT TAN**

*Product Code:  
1550*

## Description

- Watertight, crushproof, and dust proof
- Retractable extension handle
- Strong polyurethane wheels with stainless steel bearings
- Easy open Double Throw latches
- Open cell core with solid wall design - strong, light weight O-ring seal
- Automatic Pressure Equalization Valve
- Comfortable rubber over-molded top and side handles
- Stainless steel hardware and padlock protectors
- 2 Level Pick 'N' Pluck™ with convoluted lid foam
- Personalized nameplate service available
- Unconditional Lifetime Guarantee of Excellence
- FAA maximum carry on size

## Technical Specs

- Exterior Dimensions (L x W x D): 20 5/8 x 16 7/8 x 8 1/8
- Interior Dimensions (L x W x D): 18 7/16 x 14 x 7 5/8
- Weight With Foam: 11.9 lbs.
- Weight Without Foam: 10.58 lbs.
- Shipping Dimensions (L x W x D): 21" x 18" x 9"
- Shipping Weight: 15.17 lbs.

## Pelican Watertight Cases



**New & Improved Latches.**

- 1120 Guard Box®
- 1150 Case™
- 1200 Case™
- 1300 Case™
- 1400 Case™
- 1450 Case™
- 1470 Case™
- 1470 Case™
- 1490 Case™
- 1500 Case™
- 1520 Case™
- 1550 Case™
- 1600 Case™
- 1620 Case™
- 1650 Case™
- 1700 Travel VaultIII®
- 1750 Travel Vault®



Platt#	Inside Dim.			Outside Dim.			Ship Weight
	L	W	D	L	W	D	
<b>0350</b>	20"	20"	18 <sup>1</sup> / <sub>4</sub> "	22 <sup>1</sup> / <sub>2</sub> "	22 <sup>7</sup> / <sub>16</sub> "	21 <sup>1</sup> / <sub>4</sub> "	26 lbs.
<b>0370</b>	24 <sup>1</sup> / <sub>4</sub> "	24"	23"	25 <sup>1</sup> / <sub>4</sub> "	26 <sup>1</sup> / <sub>2</sub> "	26 <sup>1</sup> / <sub>2</sub> "	30 lbs.
<b>1010</b>	4 <sup>5</sup> / <sub>16</sub> "	2 <sup>13</sup> / <sub>16</sub> "	1 <sup>5</sup> / <sub>8</sub> "	5 <sup>7</sup> / <sub>16</sub> "	4 <sup>1</sup> / <sub>16</sub> "	2 <sup>1</sup> / <sub>8</sub> "	3.2 lbs.
<b>1020</b>	5 <sup>1</sup> / <sub>4</sub> "	3 <sup>1</sup> / <sub>2</sub> "	1 <sup>5</sup> / <sub>8</sub> "	6 <sup>3</sup> / <sub>8</sub> "	4 <sup>3</sup> / <sub>4</sub> "	2 <sup>1</sup> / <sub>8</sub> "	4 lbs.
<b>1030</b>	6 <sup>3</sup> / <sub>8</sub> "	2 <sup>5</sup> / <sub>8</sub> "	2"	7 <sup>1</sup> / <sub>2</sub> "	3 <sup>7</sup> / <sub>8</sub> "	2 <sup>7</sup> / <sub>16</sub> "	4.24 lbs.
<b>1040</b>	6 <sup>7</sup> / <sub>16</sub> "	3 <sup>13</sup> / <sub>16</sub> "	1 <sup>11</sup> / <sub>16</sub> "	7 <sup>1</sup> / <sub>2</sub> "	5 <sup>1</sup> / <sub>16</sub> "	2 <sup>1</sup> / <sub>8</sub> "	4.85 lbs.
<b>1050</b>	6 <sup>7</sup> / <sub>16</sub> "	3 <sup>13</sup> / <sub>16</sub> "	2 <sup>11</sup> / <sub>16</sub> "	7 <sup>1</sup> / <sub>2</sub> "	5 <sup>1</sup> / <sub>16</sub> "	3 <sup>1</sup> / <sub>8</sub> "	6.4 lbs.
<b>1060</b>	8 <sup>5</sup> / <sub>16</sub> "	4 <sup>5</sup> / <sub>16</sub> "	2 <sup>3</sup> / <sub>16</sub> "	9 <sup>3</sup> / <sub>8</sub> "	5 <sup>9</sup> / <sub>16</sub> "	2 <sup>5</sup> / <sub>8</sub> "	6.88 lbs.
<b>1120WF</b>	7 <sup>3</sup> / <sub>8</sub> "	4 <sup>7</sup> / <sub>8</sub> "	3 <sup>1</sup> / <sub>16</sub> "	8 <sup>1</sup> / <sub>4</sub> "	6 <sup>9</sup> / <sub>16</sub> "	3 <sup>9</sup> / <sub>16</sub> "	11.2 lbs.
<b>1150WF</b>	8 <sup>3</sup> / <sub>8</sub> "	5 <sup>7</sup> / <sub>8</sub> "	3 <sup>9</sup> / <sub>16</sub> "	9 <sup>1</sup> / <sub>4</sub> "	7 <sup>9</sup> / <sub>16</sub> "	4 <sup>3</sup> / <sub>8</sub> "	2.5 lbs.
<b>1200WF</b>	9 <sup>3</sup> / <sub>8</sub> "	7 <sup>1</sup> / <sub>4</sub> "	4 <sup>1</sup> / <sub>16</sub> "	10 <sup>5</sup> / <sub>8</sub> "	9 <sup>11</sup> / <sub>16</sub> "	4 <sup>7</sup> / <sub>8</sub> "	3 lbs.
<b>1300WF</b>	9 <sup>3</sup> / <sub>8</sub> "	7 <sup>1</sup> / <sub>4</sub> "	6 <sup>1</sup> / <sub>8</sub> "	10 <sup>5</sup> / <sub>8</sub> "	9 <sup>11</sup> / <sub>16</sub> "	6 <sup>7</sup> / <sub>8</sub> "	3.5 lbs.
<b>1400WF</b>	12"	9 <sup>1</sup> / <sub>16</sub> "	5 <sup>3</sup> / <sub>16</sub> "	13 <sup>3</sup> / <sub>8</sub> "	11 <sup>5</sup> / <sub>8</sub> "	6"	5.5 lbs.
<b>1420WF</b>	13"	5"	10"	15"	8 <sup>1</sup> / <sub>2</sub> "	10 <sup>1</sup> / <sub>2</sub> "	5.5 lbs.
<b>1450WF</b>	14 <sup>13</sup> / <sub>16</sub> "	10 <sup>3</sup> / <sub>8</sub> "	6"	16"	13"	6 <sup>7</sup> / <sub>8</sub> "	7.5 lbs.
<b>1470WF</b>	15 <sup>5</sup> / <sub>4</sub> "	10 <sup>9</sup> / <sub>16</sub> "	3 <sup>3</sup> / <sub>4</sub> "	16 <sup>11</sup> / <sub>16</sub> "	13 <sup>1</sup> / <sub>16</sub> "	4 <sup>3</sup> / <sub>8</sub> "	7.8 lbs.
<b>1470CC#1</b>	15 <sup>3</sup> / <sub>4</sub> "	10 <sup>9</sup> / <sub>16</sub> "	3 <sup>3</sup> / <sub>4</sub> "	16 <sup>11</sup> / <sub>16</sub> "	13 <sup>1</sup> / <sub>16</sub> "	4 <sup>3</sup> / <sub>8</sub> "	6.8 lbs.
<b>1470CC#2</b>	15 <sup>3</sup> / <sub>4</sub> "	10 <sup>9</sup> / <sub>16</sub> "	3 <sup>3</sup> / <sub>4</sub> "	16 <sup>11</sup> / <sub>16</sub> "	13 <sup>1</sup> / <sub>16</sub> "	4 <sup>3</sup> / <sub>8</sub> "	6.75 lbs.
<b>1470AC</b>	15 <sup>5</sup> / <sub>4</sub> "	10 <sup>9</sup> / <sub>16</sub> "	3 <sup>3</sup> / <sub>4</sub> "	16 <sup>11</sup> / <sub>16</sub> "	13 <sup>1</sup> / <sub>16</sub> "	4 <sup>3</sup> / <sub>8</sub> "	6.75 lbs.
<b>1490WF</b>	17 <sup>7</sup> / <sub>8</sub> "	11 <sup>1</sup> / <sub>2</sub> "	4 <sup>1</sup> / <sub>8</sub> "	19 <sup>7</sup> / <sub>16</sub> "	13 <sup>15</sup> / <sub>16</sub> "	4 <sup>11</sup> / <sub>16</sub> "	6.5 lbs.
<b>1490CC#1</b>	17 <sup>7</sup> / <sub>8</sub> "	11 <sup>1</sup> / <sub>2</sub> "	4 <sup>1</sup> / <sub>2</sub> "	19 <sup>7</sup> / <sub>16</sub> "	13 <sup>15</sup> / <sub>16</sub> "	4 <sup>11</sup> / <sub>16</sub> "	8.3 lbs.
<b>1490CC#2</b>	17 <sup>7</sup> / <sub>8</sub> "	11 <sup>1</sup> / <sub>2</sub> "	4 <sup>1</sup> / <sub>2</sub> "	19 <sup>7</sup> / <sub>16</sub> "	13 <sup>15</sup> / <sub>16</sub> "	4 <sup>11</sup> / <sub>16</sub> "	8.25 lbs.
<b>1490AC</b>	17 <sup>7</sup> / <sub>8</sub> "	11 <sup>1</sup> / <sub>2</sub> "	4 <sup>1</sup> / <sub>8</sub> "	19 <sup>7</sup> / <sub>16</sub> "	13 <sup>15</sup> / <sub>16</sub> "	4 <sup>11</sup> / <sub>16</sub> "	8.25 lbs.
<b>1500WF</b>	17"	11 <sup>7</sup> / <sub>16</sub> "	6 <sup>1</sup> / <sub>8</sub> "	18 <sup>1</sup> / <sub>2</sub> "	14 <sup>1</sup> / <sub>16</sub> "	6 <sup>7</sup> / <sub>8</sub> "	8.85 lbs.
<b>1504*</b>	17"	11 <sup>7</sup> / <sub>16</sub> "	6 <sup>1</sup> / <sub>8</sub> "	18 <sup>1</sup> / <sub>2</sub> "	14 <sup>1</sup> / <sub>16</sub> "	6 <sup>7</sup> / <sub>8</sub> "	8.85 lbs.
<b>1510</b>	20 <sup>3</sup> / <sub>16</sub> "	11 <sup>3</sup> / <sub>8</sub> "	7 <sup>1</sup> / <sub>2</sub> "	22"	14"	9"	13.9 lbs.
<b>1520WF</b>	17 <sup>7</sup> / <sub>8</sub> "	12 <sup>3</sup> / <sub>4</sub> "	6 <sup>3</sup> / <sub>4</sub> "	19 <sup>1</sup> / <sub>8</sub> "	15 <sup>7</sup> / <sub>16</sub> "	7 <sup>9</sup> / <sub>16</sub> "	10.75 lbs.
<b>1524*</b>	17 <sup>7</sup> / <sub>8</sub> "	12 <sup>3</sup> / <sub>4</sub> "	6 <sup>3</sup> / <sub>4</sub> "	19 <sup>1</sup> / <sub>8</sub> "	15 <sup>7</sup> / <sub>16</sub> "	7 <sup>9</sup> / <sub>16</sub> "	10.75 lbs.
<b>1526**</b>	17 <sup>7</sup> / <sub>8</sub> "	12 <sup>3</sup> / <sub>4</sub> "	6 <sup>3</sup> / <sub>4</sub> "	19 <sup>1</sup> / <sub>8</sub> "	15 <sup>7</sup> / <sub>16</sub> "	7 <sup>9</sup> / <sub>16</sub> "	10.75 lbs.
<b>1527+</b>	17 <sup>3</sup> / <sub>4</sub> "	13 <sup>1</sup> / <sub>2</sub> "	7 <sup>1</sup> / <sub>4</sub> "	19 <sup>1</sup> / <sub>8</sub> "	15 <sup>7</sup> / <sub>16</sub> "	7 <sup>9</sup> / <sub>16</sub> "	10.75 lbs.
<b>1550WF</b>	18 <sup>3</sup> / <sub>4</sub> "	14 <sup>3</sup> / <sub>8</sub> "	7 <sup>3</sup> / <sub>8</sub> "	20 <sup>3</sup> / <sub>8</sub> "	16 <sup>7</sup> / <sub>8</sub> "	8 <sup>3</sup> / <sub>8</sub> "	13.5 lbs.
<b>1600WF</b>	21 <sup>3</sup> / <sub>4</sub> "	16 <sup>13</sup> / <sub>16</sub> "	7 <sup>7</sup> / <sub>8</sub> "	24 <sup>1</sup> / <sub>4</sub> "	19 <sup>7</sup> / <sub>16</sub> "	8 <sup>11</sup> / <sub>16</sub> "	16 lbs.
<b>1610WF</b>	22 <sup>3</sup> / <sub>16</sub> "	17 <sup>1</sup> / <sub>8</sub> "	10 <sup>9</sup> / <sub>16</sub> "	24 <sup>9</sup> / <sub>16</sub> "	19 <sup>5</sup> / <sub>16</sub> "	11 <sup>15</sup> / <sub>16</sub> "	25.5 lbs.
<b>1620WF</b>	22 <sup>7</sup> / <sub>16</sub> "	17"	12 <sup>9</sup> / <sub>16</sub> "	24 <sup>13</sup> / <sub>16</sub> "	19 <sup>3</sup> / <sub>8</sub> "	13 <sup>7</sup> / <sub>8</sub> "	27 lbs.
<b>1650WF</b>	29"	17 <sup>7</sup> / <sub>8</sub> "	10 <sup>1</sup> / <sub>2</sub> "	32 <sup>3</sup> / <sub>4</sub> "	20 <sup>1</sup> / <sub>2</sub> "	11 <sup>5</sup> / <sub>16</sub> "	30 lbs.
<b>1660WF</b>	29 <sup>1</sup> / <sub>8</sub> "	20 <sup>11</sup> / <sub>16</sub> "	17 <sup>5</sup> / <sub>8</sub> "	31 <sup>1</sup> / <sub>2</sub> "	22 <sup>7</sup> / <sub>8</sub> "	18 <sup>7</sup> / <sub>8</sub> "	49 lbs.
<b>1700WF</b>	35 <sup>5</sup> / <sub>4</sub> "	13 <sup>13</sup> / <sub>16</sub> "	5 <sup>1</sup> / <sub>4</sub> "	31 <sup>1</sup> / <sub>8</sub> "	17 <sup>13</sup> / <sub>16</sub> "	6 <sup>1</sup> / <sub>8</sub> "	19 lbs.
<b>1720WF</b>	42"	13 <sup>1</sup> / <sub>2</sub> "	5 <sup>1</sup> / <sub>4</sub> "	44 <sup>3</sup> / <sub>8</sub> "	16"	6 <sup>1</sup> / <sub>8</sub> "	21.15 lbs.
<b>1750WF</b>	50 <sup>1</sup> / <sub>2</sub> "	13 <sup>7</sup> / <sub>16</sub> "	5 <sup>1</sup> / <sub>4</sub> "	53"	17 <sup>7</sup> / <sub>16</sub> "	6 <sup>1</sup> / <sub>16</sub> "	25.65 lbs.

### Pelican Protector® Watertight Equipment Cases

Watertight and airtight to 30 feet for the ultimate in protection. Constructed of light-weight space-age structural resin with a neoprene O-ring seal and exclusive purge valve. Supplied complete with pre-scored pick-n-pluck foam or padded dividers (no cutting required). Also includes locking flanges, massive multiple latches for absolute security and a comfortable molded fold-down handle. Custom colors and foam inserts fabricated on special order.

#1700 and #1750 supplied with regular foam. Pick-n-pluck is not available.

\*Case With Padded Dividers \*\*Case With Travel Bag +Travel Bag Only

## Pelican Flashlights

### PELICAN® FLASHLIGHTS

Platt carries a complete line of Pelican® Flashlights. Please call Platt



1900C



2400C

### PELICAN® 100% GUARANTEE

Unconditional lifetime guarantee of excellence by Pelican® Products, Inc.

## Pelican Tool Case



Platt#	Inside Dim.		
	L	W	D
<b>1520T-CB</b>	17 <sup>7</sup> / <sub>8</sub> "	12 <sup>3</sup> / <sub>4</sub> "	6 <sup>3</sup> / <sub>4</sub> "

### PELICAN® FEATURES

Pelican protector case is now available as a Platt tool case. This case is constructed of high impact co-polymer resin with a pressure relief valve and padlock loops. Meets MIL-STD 4150 for stacking, drop test and chemical attack.

This case is not watertight.