Platt Luggage, Inc.

<u>Home</u> > <u>WATERTIGHT CASES</u> > 1650 CASE



EQUIPMENT NOT INCLUDED

Contact Your Local Distributor For Pricing Colors Available: BLACK, OD GREEN, DESERT TAN

Product Code: 1650

Description

- Watertight, crushproof, and dust proof
- Open cell core with solid wall design strong, light weight
- Automatic Pressure Equalization Valve
- O-ring seal
- Comfortable rubber over-molded handle
- Stainless steel hardware and padlock protectors
- 2 level Pick 'N' PluckTM with convoluted lid foam
- Personalized nameplate service available
- Unconditional Lifetime Guarantee of Excellence
- Fold down handles
- Retractable extension handle
- 4 Strong polyurethane wheels with stainless steel bearings

Technical Specs

- Exterior Dimensions (L x W x D):30 3/4 x 20 1/2 x 11 5/8
- Interior Dimensions (L x W x D): 28 1/2 x 17 3/8 x 10 1/2
- Weight With Foam: 35.49 lbs.
- Weight Without Foam: 29.1 lbs.
- Shipping Dimensions (L x W x D): 32" x 21" x 12"
- Shipping Weight: 30.10 lbs.

Pelican Watertight Cases





Watertight and airtight to 30 feet for the ultimate in protection. Constructed of light-weight space-age structural resin with a neoprene O-ring seal and exclusive purge valve. Supplied complete with pre-scored pick-n-pluck foam or padded dividers (no cutting required). Also includes locking flanges, massive multiple latches for absolute security and a comfortable molded fold-down handle. Custom colors and foam inserts fabricated on special order.

#1700 and #1750 supplied with regular foam. Pick-n-pluck is not available.

	5 000 mmm

		-			-		
Platt#	In	side Dir	n.	Ou	tside D	im.	Ship
	L	W	D	L	W	D	Weight
0350	20"	20"	181/2"	221/2"	227/16"	211/4"	26 lbs.
0370	241/4"	24"	23"	251/4"	261/2"	261/2"	30 lbs.
1010	4 5/16"	213/16"	15/8"	57/16"	41/16"	21/8"	3.2 lbs.
1020	51/4"	31/2"	15/8"	$6^{3}/_{8}$ "	43/4"	21/8"	4 lbs.
1030	$6^{3}/_{8}$ "	25/8"	2"	71/2"	37/8"	27/16"	4.24 lbs.
1040	67/16"	313/16"	111/16"	71/2"	51/16"	21/8"	4.85 lbs.
1050	67/16"	313/16"	211/16"	71/2"	51/16"	31/8"	6.4 lbs.
1060	85/16"	45/16"	23/16"	$9^{3}/_{8}$ "	59/16"	25/8"	6.88 lbs.
1120WF	$7^{3}/_{8}$ "	$4^{7}/_{8}$ "	31/16"	81/4"	69/16"	39/16"	11. 2 lbs.
1150WF	$8^{3}/_{8}$ "	57/8"	39/16"	$9^{1}/_{4}$ "	79/16"	$4^{3}/_{8}$ "	2.5 lbs.
1200WF	$9^{3}/_{8}$ "	71/4"	41/16"	105/8"	$9^{11}/_{16}$ "	$4^{7}/_{8}$ "	3 lbs.
1300WF	$9^{3}/_{8}"$	71/4"	61/8"	$10^{5}/8"$	$9^{11}/_{16}$ "	$6^{7}/_{8}$ "	3.5 lbs.
1400WF	12"	$9^{1}/_{16}$ "	53/16"	$13^{3}/_{8}$ "	$11^{5}/_{8}$ "	6"	5.5 lbs.
1420WF	13"	5"	10"	15"	81/2"	$10^{1/2}$ "	5.5 lbs.
1450WF	$14^{13}/_{16}$ "	$10^{3}/8$ "	6"	16"	13"	$6^{7}/_{8}$ "	7.5 lbs.
1470WF	153/4"	109/16"	33/4"	$16^{11}/_{16}$ "	$13^{1}/_{16}$ "	$4^{3}/_{8}$ "	7.8 lbs.
1470CC#1	153/4"	109/16"	33/4"	$16^{11}/_{16}$ "	$13^{1}/_{16}$ "	$4^{3}/_{8}$ "	6.8 lbs.
1470CC#2	$15^{3}/_{4}$ "	109/16"	33/4"	1611/16"	$13^{1}/_{16}$ "	$4^{3}/_{8}$ "	6.75 lbs.
1470AC	153/4"	109/16"	33/4"	$16^{11}/_{16}$ "	$13^{1}/_{16}$ "	$4^{3}/_{8}$ "	6.75 lbs.
1490WF	$17^{7}/_{8}$ "	111/2"	41/8"	$19^{7}/_{16}$ "	$13^{15}/_{16}$ "	$4^{11}/_{16}$ "	6.5 lbs.
1490CC#1	$17^{7}/8"$	111/2"	41/2"	$19^{7}/_{16}$ "	1315/16"	$4^{11}/_{16}$ "	8.3 lbs.
1490CC#2	$17^{7}/_{8}$ "	111/2"	41/2"	$19^{7}/_{16}$ "	$13^{15}/_{16}$ "	$4^{11}/_{16}$ "	8.25 lbs.
1490AC	$17^{7}/_{8}$ "	111/2"	41/8"	$19^{7}/_{16}$ "	$13^{15}/_{16}$ "	$4^{11}/_{16}$ "	8.25 lbs.
1500WF	17"	11 7/16"	$6^{1}/_{8}$ "	181/2"	$14^{1}/_{16}$ "	$6^{7}/_{8}$ "	8.85 lbs.
1504*	17"	11 7/16"	61/8"	181/2"	$14^{1}/_{16}$ "	$6^{7}/_{8}$ "	8.85 lbs.
1510	$20^{3}/_{16}$ "	$11^{3}/_{8}$ "	71/2"	22"	14"	9"	13.9 lbs.
1520WF	$17^{7}/8$ "	12 3/4"	$6^{3}/_{4}$ "	$19^{1}/8"$	157/16"	79/16"	10.75 lbs.
1524*	$17^{7}/_{8}$ "	12 3/4"	63/4"	$19^{1}/_{8}$ "	$15^{7}/_{16}$ "	79/16"	10.75 lbs.
1526**	$17^{7}/_{8}$ "	12 3/4"	63/4"	$19^{1}/_{8}$ "	$15^{7}/_{16}$ "	79/16"	10.75 lbs.
1527+	$17^{3}/_{4}$ "	131/2"	71/4"	$19^{1}/8"$	157/16"	79/16"	10.75 lbs.
1550WF	$18^{3}/_{4}$ "	$14^{3}/_{8}$ "	$7^{5}/_{8}$ "	$20^{5}/_{8}$ "	$16^{7}/_{8}$ "	$8^{1}/_{8}$ "	13.5 lbs.
1600WF	213/4"	$16^{13}/_{16}$ "	$7^{7}/_{8}$ "	241/4"	$19^{7}/_{16}$ "	811/16"	16 lbs.
1610WF	$22^{3}/_{16}$ "	171/8"	109/16"	249/16"	195/16"	1115/16"	25.5 lbs.
1620WF	$22^{1}/_{16}$ "	17"	129/16"	$24^{13}/_{16}$ "	$19^{3}/_{8}$ "	$13^{7}/_{8}$ "	27 lbs.
1650WF	29 "	$17^{7}/_{8}$ "	$10^{1}/_{2}$ "	323/4"	$20^{1}/_{2}$ "	115/16"	30 lbs.
1660WF	$29^{1}/_{8}$ "	$20^{11}/_{16}$ "	175/8"	311/2"	$22^{7}/8"$	$18^{7}/8"$	49 lbs.
1700WF	353/4"	$13^{13}/_{16}$ "	51/4"	$31^{1}/_{8}$ "	$17^{13}/_{16}$ "	$6^{1}/_{8}$ "	19 lbs.
1720WF	42 "	131/2"	51/4"	$44^{3}/_{8}$ "	16"	$6^{1}/_{8}$ "	21.15 lbs.
1750WF	501/2"	137/16"	51/4"	53"	177/16"	61/16"	25.65 lbs.

*Case With Padded Dividers **Case With Travel Bag +Travel Bag Only

Pelican Flashlights

PELICAN® FLASHLIGHTS

Platt carries a complete line of Pelican® Flashlights. Please call Platt





PELICAN® 100% GUARANTEE

Unconditional lifetime guarantee of excellence by Pelican® Products, Inc.

Pelican Tool Case



Platt#	inside Dim.			
	L	W	D	
1520T-CB	$17^{7}/8$	" 12 3/4"	63/4"	

PELICAN® FEATURES

Pelican protector case is now available as a Platt tool case. This case is constructed of high impact co-polymer resin with a pressure relief valve and padlock loops. Meets MIL-STD 4150 for stacking, drop test and chemical attack.

This case is not watertight.