

HOME



SEARCH



LOCATE DEALER



LOG ON



CONTACT US



FOAM-FILLED CASES

Blow Molded



Light-Duty ABS



Medium-Duty ABS



Heavy-Duty Poly



Heavy-Duty Poly (WTH)



Heavy-Duty ATA



Heavy-Duty ATA (RWTH)



ZOOM

Blow Molded Cases

Meet Platt's low cost solution to "Make-Your-Own" case needs.

These cases are manufactured from prime, high-density polyethylene, with double wall construction. The textured exteriors resist dents, cracking and scuffs. The shells are unaffected by extreme temperatures.

The hardware features mechanical latches that are field replaceable, and a mechanical hinge system that is made to last.

All cases meet U.S. 94B Specifications as an electrical insulator and are impervious to chemical attack.

Platt Part #	Inside Dim. (L)	Inside Dim. (W)	Inside Dim. (D)	Outside Dim. (L)	Outside Dim. (W)	Outside Dim. (D)
102	5.625	3.625	1.375	6.5	4.5	1.688
103	5.625	3.625	1.875	6.5	4.5	2.125
104	7.125	4	1.438	8	5	1.75
105	7.125	4	1.938	8	5	2.125
106	7.5	5	1.688	8.5	6	2
107	7.5	5	2.188	8.5	6	2.5
108	7.5	5	2.688	8.5	6	3
202	8.5	5.5	1.688	9.5	6.5	2
203	8.5	5.5	2.688	9.5	6.5	2.5
204	8.5	5.5	2.688	9.5	6.5	3
205	8.5	5.5	3.188	9.5	6.5	3.5

FOAM-FILLED



PARALLEL RIB



WATERTIGHT



GUARDSMAN™ ATA



MOLDED TOOL



ATA TOOL



PALETS



SEWN TOOL



ATTACHÉ



CARTS



CATALOG CASES





206	9.5	6	1.938	10.5	7	2.25
207	9.5	6	2.688	10.5	7	3
208	9.5	6	3.438	9.5	7	3.75
302	10.188	6.5	1.938	11.313	7.5	2.25
303	10.188	6.5	2.688	11.313	7.5	3
304	10.188	6.5	3.438	11.313	7.5	3.75
305	11	7	1.938	12	8	2.25
306	11.5	7	2.688	12	8	3
307	11	7	3.438	12	8	3.75
308	12.375	6.875	2.875	13.5	8	3.25
309	12.375	6.875	4.063	13.5	8	4.375
310	12.375	6.875	5.188	13.5	8	5.5
402	12.375	7.875	2.875	13.5	9	3.25
403	12.375	7.875	4	13.5	9	4.375
404	12.375	7.875	5.125	13.5	9	5.5
405	12.375	5.875	2.875	13.5	10	3.25
406	12.4	8.9	4	13.5	10	4.375
407	12.375	8.875	5.125	13.5	10	5.5
503	13.875	8.875	2.875	15	10	3.25
504	13.875	8.875	4	15	10	4.375
505	13.875	8.875	5.125	15	10	5.5
506	13.875	9.875	2.875	15	11	3.25
507	13.875	9.875	4	15	11	4.375
508	13.875	9.875	5.125	15	11	5.5
604	14.875	10.375	2.875	16	11.5	3.25

605	14.875	10.375	4	16	11.5	4.375
606	14.875	10.375	5.125	16	11.5	5.5
607	15.875	10.875	2.875	17	12	3.125
608	15.875	10.875	2.875	17	12	4.375
609	15.875	10.875	5.125	17	12	5.5
610	16.875	11.688	3.875	18	13	4.25
611	16.875	11.688	5	18	13	5.375
612	16.875	11.688	6.125	18	13	6.5
705	17.875	12.688	4.375	19	14	4.75
706	17.875	12.75	5.75	19	14	6.25
707	17.875	12.75	7.125	19	14	7.5
802	21.313	14.313	6.625	23	16	7
803	21.313	14.313	9.625	23	16	10
902	25.813	14.313	6.625	27.5	16	7
903	25.813	14.313	9.625	27.5	16	10

CUSTOM FOAM AND ADDITIONAL SIZES

In addition to Platt's stock cubed foam filled cases, we can furnish custom foam interiors to fit our stock cases. Platt also has many additional case sizes available. For additional information on blow-molded cases, click [here](#) and request *Style Form BM99-1*. For additional molded case sizes, [here](#) and request *Engineering Catalog ENG99-2*.

Notes:

RH = *Recessed Hardware*

WTH = *Wheels and Telescoping Handle*

All Platt Foam-Filled cases are filled with layers of cubed foam and a flat cushion in the bottom and convoluted and/or flat cushion in the lid.