

Platt Luggage, Inc.

[Home](#) > [SPECIALTY AND MISC](#) >

HT321HW CATALOG CASE



**Colors
Available:
BLACK
Also Available
In: OXFORD**

*Product Code:
HT321HW*

Description

Patented construction features supported backed vinyl top, bottom and sides with thermoplastic end shells and clear anodized aluminum frames making it the best and longest lasting catalog case available. Concealed metal rods running length of case interconnected and riveted to end shells form a lightweight yet flexible frame. With large bottom glides for maximum wearability, outside pocket for convenience, chrome plated combo locks, and unique golf grip handle. Case also comes with wheels and telescoping handle for easy traveling.

Technical Specs

- Interior Dimensions (L x W x D): 19" x 12" x 8"
- Exterior Dimensions (L x W x D): 21 1/2" x 16" x 9 1/2"
- Shipping Dimensions (L x W x D): 23" x 18" x 10"
- Shipping Weight: 11.20 lbs.

Catalog Cases



Catalog Cases

Patented construction features nylon-backed vinyl top, bottom and sides. Thermoplastic end shells and clear anodized aluminum frames give superior support, making it the best and longest lasting catalog case available. Concealed metal rods running length of case interconnected and riveted to end shells form a lightweight yet flexible frame. With large bottom glides for maximum wearability, outside pocket for convenience, chrome plated combination locks and unique golf grip handle.

Platt#	Inside Dim.			Colors
	L	W	D	
HT219I	17"	12"	8"	Oxford
HT319I	17"	12"	8"	Black
HT221I	19"	12"	8"	Oxford
HT321I	19"	12"	8"	Black

Fabricated Static-Free PCB Cases



Static-Free PCB Cases

Exterior is static-free black cotton duck and anti-static blue poly end shells inter-locked and riveted to an aluminum frame for maximum strength. Two combination locks, golf grip handle, and giant studs for wearability. Interior features our unique adjustable static-free environment with cushioned separators. Platt cases incorporate Dry Stat/Cryovac EPG 112 humidity independent, amine free static dissipative material and Cancel amine free open cell cushion materials that meet or exceed Military specifications MIL-B-81705, Type II and PPP-C-1842A, Type III. With grounding snap. The number of slots determines the amount of board space available in each case. All but the 12-PCB have two dividers for enhanced board storage.

Platt#	Inside Dim.			Slots
	L	W	D	
12-PCB	12"	12"	8"	7
21-PCB	21"	12"	8"	7
24-PCB	17"	14"	13"	11
29-PCB	23"	18"	8"	9



Aerosol Can Sample Case



Detail of inside bottom molded insert for 639.

Aerosol Can Sample Cases

Molded of black ABS thermoplastic exterior with extruded aluminum frame, drawbolt key locks, and molded handle. Interior is custom molded to hold 8 cans.

Platt#	Inside Dim.		
	L	W	D
639	19"	13"	4"

Slide Carousel Projector Case



Slide Carousel Projector Case

ABS thermoplastic exterior with extruded aluminum frame, drawbolt key locks and molded handle. Interior custom formed to fit Ektagraphic series 4000 and 5000 series.

Platt#	Inside Dim.		
	L	W	D
1913	19"	13"	7"

Divider Boxes



Infinite Divider Boxes

The ultimate storage container for small parts. Dividers are moveable in 1/16" increments providing flexibility in organized space. Resistant to oil, solvents and most common chemicals. Sold in master pack quantity only.

Platt#	Dim.			#Dividers
	L	W	D	
PB300	6 ³ / ₈ "	3 ³ / ₈ "	1 ¹ / ₄ "	6
PB600	10 ¹ / ₂ "	6 ¹ / ₂ "	1 ¹ / ₂ "	6
PB900	13 ¹ / ₈ "	8 ³ / ₄ "	1 ⁷ / ₈ "	16

"Quality That Lasts"