

H.K. Porter

HKE500 Series, 5-HP Power Pack Only - Operation of One Workhead

Product Details

Catalog No.	HKE5002A
UPC Code	037103238290
Weight	215 lbs.
Horsepower	5 HP
Number of Outlets	Single
Maximum Operating Pressure	7,800 psi
Voltage/Phase/Hertz	230 V 3 PH 60 Hz
Low Voltage Control	Yes
Operation Type	Production Duty
Packaging	No Item Level Packaging/No UPC
Stock Item	Made to Order-Call for Lead Time

Package Details (Dimensions)

[Email this Page](#)

Product Features:

- **5 HP TEFC motor for dependable operation, low voltage (24 VAC)**
- **Lightweight design, rugged construction**
- **2-stage pump delivers low pressure for rapid advance of piston**
- **Pump shifts to high pressure under load. Large, 2.5 gallon reservoir**
- **Internal relief valve protects system components from overload**
- **Internal filter protects system from contamination of hydraulic oil**
- **Control option A: Push-button control handle attached to workhead W10824**
- **Control option B: Heavy-duty foot switch W32368**
- **Control option C: Hand-held, control switch W36048**
- **NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!**