


VECTORBORD® PLUGBORD™ PART NO. : 4610-1



Description :
4.5" X 6.5" X 0.062, Hole Dia.: 0.042", Grid: 0.100" X 0.100"
Contacts Only
Unrestricted component placement over entire board surface
Layout paper and instructions included.

Circuit Pattern :	3-Hole Solder Pad
Contacts :	28/56 @ 0.125" Centers Ni / Gold
16 Pin DIP Capacity :	59
Hole Diameter :	0.042" { 1.0668 mm }
Grid :	0.100" X 0.100" { 2.54mm X 2.54mm }
Dimension { H, W, T } :	4.5" X 6.5" X 0.062"
Material :	FR-4
Wire-Wrap Terminals :	T44, T46, T49 & T68
Solder Connector :	R656-1
Wire-Wrap Socket Pins :	R32
Wire-Wrap Connector :	R656
Extender :	3690-16
Recommended Card Cage:	CCK 13 Series Card Cage { Subracks }
UL Flammability Class :	94V - 0