

Accessories

Series R600 Edge Connectors

This section contains parts and accessories for Vectorbord products. They are useful for board-level prototyping and breadboarding. Prototypes are created in various ways; by computer design or by hand - but with one thing in common: sooner or later, you have to make a physical board. It is at this stage that Vectorbord and these parts and accessories may be useful to you. They are selected for convenience and utility and they are readily available from local Vector distributors.



- Wire-Wrap .025" Sq. R656-3 56 Contacts
- Allows 3 level wraps
- Use 28 to 32 AWG wire
- STD bus






Accessories

Style 1



- Solder tail (with eyelet) R656-1 Solder
- Solder eyelet type
- R644C Center Mounting Ears
- R644F Flush Mounting (as shown in illustration)




65



Accessories Series R600 Edge Connectors



- Solder tail leads for mother boards & backplanes with special .140" row spacing
- R656-2: for backplane applications



Style 3

Flushmount

Specifications

Solder Type Insulator Material:

Wire-Wrap Type Insulator:

Contact Material: Contact Plating: Test Voltage: Rated Current: Contact Res. Drop: Insulation Resistance: Phenolic, UL-94V-0 or glass filled Diallylphthalate UL-94V-1 or Ryton R10 or equivalent Phenolic, UL-94V-0 or glass filled Diallylphthalate UL-94V-1 or Polyester (VALOX) or equivalent UL-94V-0. Phosphor bronze QQ-B-750 .000010" gold over .000050" nickel 650 VAC 3 AMPS 30 mV Max. @ rated current 5000 ohms nominal @ 500 VDC

Ordering Information

	Part No.	No. of Contacts	Termination Type	Mounting Ears	Style #	Α	В	С	D	Е	F	G	н	I	J	к	L
essorie:	R630	30	Solder Tail	Center	2	.156"	2.504"	2.65"	2.938"	3.270"	.41"	.200"	.47"	n/a	.25"	.34"	.25"
	R636-1 R636-2	72	Wire-Wrap Solder Tail	Center	1	.100" .100"	3.707" 3.707"	3.88" 3.88"	4.175" 4.175"	4.475" 4.475"	.41" .41"	.200"	.62" .47"	.55"	.25" .25"	.34" .34"	.65" .25"
	R636-2	72 44	Solder Tail	Flush Flush	2 2	.100	3.707 3.596"	3.88 3.75"	4.175 4.032"	4.475 4.360"	.41 .41"	.200" .200"	.47 .47"	n/a .25"	.25 .25"	.34 .265"	.25
	R644-2	44	Wire-Wrap	Center	1	.100"	2.300"	2.55"	2.850"	3.120"	.41"	.200"	.62"	.55"	.25"	.297"	.65"
	R644-3C	44	Wire-Wrap	Center	1	.156"	3.596"	3.75"	4.032"	4.360"	.41"	.200"	.62"	.55"	.25"	.384"	.65"
	R644-3F	44	Wire-Wrap	Flush	1	.156"	3.596"	3.75"	4.032"	4.360"	.41"	.200"	.62"	.55"	.25"	.384"	.65"
	R656-1	56	Solder Tail	Flush	2	.125"	3.625"	3.79"	4.045"	4.336"	.41"	.200"	.47"	n/a	.25"	.34"	.25"
	R656-2	56	Wire-Wrap	Center	1	.125"	3.625"	3.79"	4.045"	4.325"	.41"	.250"	.62"	.55"	.25"	.34"	.22"
	R680-1	80	Wire-Wrap	Center	1	.125"	5.125"	5.29"	5.545"	5.805"	.41"	.250"	.62"	.55"	.25"	.34"	.65"
	R680-2	80	Solder Tail	Center	2	.125"	5.125"	5.29"	5.545"	5.805"	.41"	.200"	.62"	.55"	.25"	.34"	.65"
	R681-2	100	Wire-Wrap	Center	3	.125"	6.375"	6.54"	6.795"	7.065"	.41"	.250"	7.065"	.55"	.25"	.34"	.22"
	R681-3	100	Solder Tail	Center	2	.125"	6.375"	6.54"	6.795"	7.065"	.41"	.200"	.47"	n/a	.25"	.34"	.25"
	R683	62	Solder Tail	Flush	3	.100"	2.06"	2.06"	n/a	2.06"	.41"	.200"	.61"	n/a	.25"	.295"	.20"



A Fine Technology Group Specifications subject to change without notice.