Xcelite

5.45" Hard Wire (Piano and Music) Cutter with Blue Cushion Grip Handles



Product Details

Catalog No. 134CG

UPC Code 037103059994

Description Transverse End Cutter

Jaw Type Flush

Jaw Length 9/16 in.

Head Width 23/32 in.

Head Thickness 21/64 in.

Tip Dimensions Not Measured

Packaging Industrial Box/Carton

Tech. Spec. <u>134CG_Specifications.pdf</u>

Low Res. Image <u>134CG_100.jpg</u>

High Res. Image 134CG_300.jpg

Stock Item Normal Stock Item

Package Details (Dimensions)

Product Features:

- Shear cutting action
- Ensures square cut ends
- Captures material on both sides of jaw, eliminates flying segments
- Patented spring loaded hold-down keeps material at 90° to tool blade
- Prevents material from forcing jaws apart
- Wire capacity .062"
- Stranded cable capacity 1/16"

Xcelite 5.45" Hard Wire (Piano and Music) Cutter with Blue Cushion Grip Handles



| Individual Product | | | | | | | |
|--------------------|--------------|--|--|--|--|--|--|
| Catalog No. | 134CG | | | | | | |
| UPC Code | 037103059994 | | | | | | |
| Quantity | 1 | | | | | | |
| Length (Inches) | 5.8 | | | | | | |
| Width (Inches) | 2.2 | | | | | | |
| Height (Inches) | 0.8 | | | | | | |
| Gross Weight (lb) | 0.2 | | | | | | |
| Volume (cu in) | 10.208 | | | | | | |

| Catalog No. | 134CG | | | | | | |
|-------------------|----------------|--|--|--|--|--|--|
| I 2 of 5 Code | 10037103059991 | | | | | | |
| Quantity | 6 | | | | | | |
| Length (Inches) | 6 | | | | | | |
| Width (Inches) | 5.25 | | | | | | |
| Height (Inches) | 2.375 | | | | | | |
| Gross Weight (lb) | 1.2 | | | | | | |
| Volume (cu in) | 74.813 | | | | | | |

| Catalog No. | 134CG | | | | | | |
|-------------------|----------------|--|--|--|--|--|--|
| I 2 of 5 Code | 20037103059998 | | | | | | |
| Quantity | 48 | | | | | | |
| Length (Inches) | 11.875 | | | | | | |
| Width (Inches) | 10.875 | | | | | | |
| Height (Inches) | 5.125 | | | | | | |
| Gross Weight (lb) | 9.6 | | | | | | |
| Volume (cu in) | 661.846 | | | | | | |

Pliers and Cutters - With Red Cushion Grip Handles




- The exceptional strength and performance of Xcelite® pliers and cutters are the result of forged alloy steel construction, precision machining, and scientific proportioning
- Handles designed to fit the hand comfortably and to provide maximum leverage
- Cleanly machined and perfectly aligned jaws grip tightly and surely while easy cutting is assured by hand-honed, mated cutting edges
- For extra working comfort all models have permanent, red plastic-coated "Cushion-Grip" handles except Combination Slip Joint pliers
- These high quality pliers and cutters are featured in Xcelite® Attachê Tool Cases



NOTE: When using cutting pliers always wear safety glasses to protect eyes from wire clippings

Hard Wire (Piano and Music) Cutter 134CG





- Shear cutting action
- Ensures square cut ends
- Captures material on both sides of jaw, eliminates flying segments
- Patented spring loaded hold-down keeps material at 90° to tool blade
- · Prevents material from forcing jaws apart
- Wire capacity .062
- Stranded cable capacity 1/16"

| Cat | UPC | | Len | igth | Į. | ١ | В | 3 | C | | Pack | Wt. | Shelf |
|-------|--------------|--------|------|------|------|----|------|------|------|-----|------|-----|-------|
| No. | No. | Packed | Inch | mm | Inch | mm | Inch | mm | Inch | mm | lb | g | Pack |
| 134CG | 037103059994 | Boxed | 5.45 | 140 | 0.55 | 14 | 0.72 | 18.5 | 0.32 | 8.2 | 18.4 | 522 | 6 |