60 Watt, 120v, 700°F 3-wire Soldering Iron with CT5A7 Tip



∢∢ previous	print	close	next 🕨	
Catalog No.		W60P3		
UPC Code		037103474094		
Туре	Ter	Temperature Controlled		
Wattage		100 W		
Temperature Range	60	600° F/700° F/800° F		
Cord Length		6 ft.		
Components Supplied		CT5A7		
Packaging	In	Industrial Box/Carton		
Tech. Spec.	Solo	Solder_Safety_Warnings. pdf		
Lineart		W60P.pdf		
Low Res. Image		W60P_100.jpg		
High Res. Image		W60P_300.jpg		
Stock Item		Normal Stock Item		

Package Details (Dimensions)

Email this Page

Product Features:

- Uses Weller "closed loop" method of controlling maximum tip temperature
- Portable line voltage iron no base station required
- Stainless steel modular plug-in heater, greater efficiency & versatility
- Temperature is controlled by tip-600°F, 700°F, and 800°F tips available
- Nominal heat-up time with 700°F tip is 110 seconds
- Three-wire grounded cord set
- Uses CT series tips
- Heating element type: Nichrome wound, plug in
- UL and cUL listed