


SERIES 29

FEATURES

- Flush Hole to Prevent Crimping
- Space-Saving ³/₈" Diameter or Decorative Flared Skirt
- Dual Mounting Base Accessory



DIMENSIONS In Inches (and millimeters)



SPECIFICATIONS

Rating Criteria

Rating: At 120 Vdc, 15 Amps continuously, with a maximum temperature rise of 20°C. **Insulation Resistance:** Between stud and mounting panel

For 29-1 styles 120,000 megohms For 29-3 styles 200,000 meghoms Voltage Breakdown: Between studs and mounting panel For 29-1 styles 1500 Vac

3000 Vac

For 29-1 styles For 29-3 styles

Materials and Finishes

Metal Parts: Nickel-plated brass Insulating Materials: Thermoset plastic per MIL-M-14, Type CFG

Additional Characteristics

Insulating Washers: Non-turn "D" style Solder Stud: Integral; 2 hex nuts for solder lug connections Heads: Captive Cross Hole: Flush to stud extension to eliminate cutting or crimping wires Panel Thickness: Up to ³/16" (4,76)

ORDERING INFORMATION

Order using part numbers shown in dimensions.

Available from your local Grayhill Distributor. For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.