

**H.K. Porter
24 1/2" General Purpose, Center Cut Cutter**



Product Details

Catalog No.	0190FC
UPC Code	037103907073
Weight/Length	4 1/2 lbs./24 1/2 in.
Handle Material	Fiberglass
Jaw Design/Cutting Blade	All Purpose/Center Cut
Replacement Cutterhead/Jaws	0113C
Capacity	See Tech Specs Link Below
Material Hardness	See Tech Specs Link Below
Brinell/Rockwell	See Tech Specs Link Below
Packaging	Industrial Box/Carton
Literature	<u>Safety-Hand Tool Selection.pdf</u>
Tech. Spec.	<u>0190FC Specifications.pdf</u>
Lineart	<u>0190FC.pdf</u>
Low Res. Image	<u>0190FC 100.jpg</u>
High Res. Image	<u>0190FC 300.jpg</u>
Parts List	<u>Parts for 0190FC.pdf</u>
Stock Item	Normal Stock Item

Package Details (Dimensions)

Product Features:

- All-purpose jaws with center-cut blades
- Cuts soft, medium, and hard metals
- Maximum hardness of material to be cut: Brinell 455/Rockwell C48
- Lockplate keeps jaws from loosening
- Toggle joints turn 50 lb hand pressure to 4000 lb cutting pressure
- Screw-type adjustment realigns edges
- Strong, lightweight fiberglass handles
- Popular cutter
- Replacement cutterhead: 0113C
- NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!