

**H.K. Porter
24" Heavy Duty Cutter with Keeper**

◀◀ previous print close next ▶▶



Product Details	
Catalog No.	0190MCK
UPC Code	037103907141
Weight/Length	6 1/2 lbs./24 in.
Handle Material	Tubular Steel
Jaw Design/Cutting Blade	All Purpose/Center Cut
Replacement Jaws/Heads/Blades	0113MCK
Capacity	5/16 in./8 mm
Material Type	Common/EHS Guy Strand
Packaging	Industrial Box/Carton
Literature	Safety-Hand Tool Selection.pdf
Lineart	0190MCK.pdf
Low Res. Image	0190MCK_100.jpg
High Res. Image	0190MCK_300.jpg
Parts List	Parts for 0190MCK.pdf
Stock Item	Normal Stock Item

Package Details (Dimensions)

[Email this Page](#)

Product Features:

- Center cut jaws
- Heavy-duty straps support the jaws
- Cuts hard metals and bolts, rods, bars, ACSR, and ACAR
- Lockplate keeps jaws from loosening
- Toggle joints turn 50 lb hand pressure to 4000 lb cutting pressure
- Screw-type adjustment realigns edges
- Swing-away keeper holds EHS guy wire and pre-stressed cable in position
- Prevents cable spreading or deforming, gives complete cut of all strands
- Replacement cutterhead: 0113MCK
- NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!