

H.K. Porter

36" Heavy Duty Cutter for Hard, Non-Alloy Chain 7/16" Capacity



◀◀ previous print close next ▶▶

| Product Details | |
|-----------------------------|---|
| Catalog No. | 0390MHX |
| UPC Code | 037103909367 |
| Weight/Length | 13 lbs./36 in. |
| Handle Material | Tubular Steel |
| Jaw Design/Cutting Blade | Heavy Duty/Center Cut |
| Replacement Cutterhead/Jaws | 0313HCX |
| Capacity | See Tech Specs Link Below |
| Material Hardness | See Tech Specs Link Below |
| Brinell/Rockwell | See Tech Specs Link Below |
| Packaging | Industrial Box/Carton |
| Literature | Safety- Hand Tool Selection.pdf |
| Tech. Spec. | 0390MHX Specifications.pdf |
| Lineart | 0190MHC.pdf |
| Low Res. Image | 0390MHX_100.jpg |
| High Res. Image | 0390MHX_300.jpg |
| Parts List | Parts for 0390MHX.pdf |
| Stock Item | Normal Stock Item |

Package Details (Dimensions)

Email this Page

Product Features:

- Extremely strong, durable tool
- Short-nosed jaws with high-tempered, center-cut blades
- Cuts hard, non-alloy chain
- Maximum hardness of material to be cut: Brinell 455/Rockwell C48
- Lockplate keeps jaws from loosening
- Toggle joints turn 50 lb hand pressure to 4000 lb cutting pressure

- **Screw-type adjustment realigns edges**
- **Heavy duty straps**
- **Replacement cutterhead: 0313HCX**
- **NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!**